

**CLI C 02-3 WS/SW 6 CD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|                     |                                                                       |
|---------------------|-----------------------------------------------------------------------|
| Version             | CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, white |
| Order No.           | <a href="#">1869821520</a>                                            |
| Type                | CLI C 02-3 WS/SW 6 CD                                                 |
| GTIN (EAN)          | 4032248446407                                                         |
| Qty.                | 500 pc(s).                                                            |
| Alternative product | <a href="#">1568249999</a>                                            |

Creation date January 28, 2022 5:19:33 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## CLI C 02-3 WS/SW 6 CD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 3.5 mm | Depth (inches)  | 0.138 inch |
| Height     | 3 mm   | Height (inches) | 0.118 inch |
| Width      | 3.4 mm | Width (inches)  | 0.134 inch |
| Net weight | 0.04 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|                                              |               |                                   |                                      |
|----------------------------------------------|---------------|-----------------------------------|--------------------------------------|
| Colour                                       | white         | Colour of printing                | black                                |
| Halogen                                      | Yes           | Material                          | PVC, soft, without Cadmium           |
| Material colour according to resistance code | 9             | Number of markers per combination | 1 Reel = Conductor and cable markers |
| Operating temperature range                  | -30...80 °C   | Operating temperature range, max. | 80 °C                                |
| Operating temperature range, min.            | -30 °C        | Orientation of print              | horizontal                           |
| Printed characters                           | Numbers       | Printing                          | 6                                    |
| Printing method                              | hot-embossing | Recommended industries            | Process, Machinery                   |
| Type of printing                             | Standard      | UL 94 flammability rating         | V-0                                  |
| Version                                      | CD            | Width                             | 3.4 mm                               |

## Conductor and cable markers

|                               |                     |                                  |                           |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D.                | 1.3 - 3 mm          | Conductor O.D., max.             | 3 mm                      |
| Conductor O.D., min.          | 1.3 mm              | Conductor cross-section, max.    | 1.5 mm <sup>2</sup>       |
| Conductor cross-section, min. | 0.2 mm <sup>2</sup> | Cross-section for connected wire | 0.2 - 1.5 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                           |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 |             |             |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Engineering Data            | <a href="#">EPLAN, WSCAD</a>                                         |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

### CLI C 02-3 WS/SW 6 CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1869821520](#)