

VG M40-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, M 40, 18 mm, OD min. 22 - OD max. 32 mm, Polyamide 6
Order No.	1909730000
Type	VG M40-K67
GTIN (EAN)	4032248536658
Qty.	10 pc(s).

VG M40-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	69.5 mm	Length (inches)	2.736 inch
Net weight	78.1 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size 1	53 mm	Cable glands	metric
External thread	M 40	Length of thread	18 mm
Material	Polyamide 6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	32 mm
Outer cable diameter, min.	22 mm	Pitch of thread	1.5 mm
Protection degree	IP67	Seal insert	NBR
Standards	EN/IEC 62444	Tightening torque	5 Nm
Torque for cap nut, max.	20.5 Nm	Torque for cap nut, min.	19.5 Nm
Torque for connecting adapter, max.	5.5 Nm	Torque for connecting adapter, min.	4.5 Nm
Torque for lock nut, max.	5.5 N/m	Torque for lock nut, min.	4.5 N/m
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

VG M40-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Plastic lock nuts, grey**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M40 - K GR	Version
Order No.	1772490000	SKMU PA (plastic locknut), Locknut, M 40, 7 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4032248130238	GF30)
Qty.	50 pc(s).	

Polyethylene flat gasket - GWDR PO

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M40-PO	Version
Order No.	1777970000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 40, Polyethylene
GTIN (EAN)	4032248158232	
Qty.	50 pc(s).	

VG M40-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Neoprene flat gasket - GWDR NP**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M40-NP	Version
Order No.	1736270000	GWDR NP (flat gasket - neoprene), Sealing ring, M 40, Neoprene
GTIN (EAN)	4008190956066	
Qty.	20 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1909730000](#)