

VG PG16-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, PG 16, 10 mm, OD min. 10 - OD max. 14 mm, Polyamide 6
Order No.	1909800000
Type	VG PG16-K67
GTIN (EAN)	4032248536726
Qty.	50 pc(s).

VG PG16-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	41 mm	Length (inches)	1.614 inch
Net weight	12.38 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size 1	27 mm	Cable glands	PG
External thread	PG 16	Length of thread	10 mm
Material	Polyamide 6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	14 mm
Outer cable diameter, min.	10 mm	Protection degree	IP67
Seal insert	NBR	Tightening torque	3.5 Nm
Torque for cap nut, max.	6 Nm	Torque for cap nut, min.	5 Nm
Torque for connecting adapter, max.	4 Nm	Torque for connecting adapter, min.	3 Nm
Torque for lock nut, max.	4 N/m	Torque for lock nut, min.	3 N/m
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

VG PG16-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Plastic lock nuts, grey



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG16-K GR	Version
Order No.	1697480000	SKMU PA (plastic locknut), Locknut, PG 16, 6 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4008190880590	GF30)
Qty.	100 pc(s).	

Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG16-PO	Version
Order No.	1719480000	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 16,
GTIN (EAN)	4008190352745	Polyethylene
Qty.	100 pc(s).	

VG PG16-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG16-NP	Version
Order No.	1719580000	GWDR NP (flat gasket - neoprene), Sealing ring, PG 16, Neoprene
GTIN (EAN)	4008190352844	
Qty.	100 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1909800000](#)