

VG PG36-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, PG 36, 13 mm, OD min. 22 - OD max. 32 mm, Polyamide 6
Order No.	1909830000
Type	VG PG36-K67
GTIN (EAN)	4032248536757
Qty.	10 pc(s).

VG PG36-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	64.5 mm	Length (inches)	2.539 inch
Net weight	65.9 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size 1	53 mm	Cable glands	PG
External thread	PG 36	Length of thread	13 mm
Material	Polyamide 6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	32 mm
Outer cable diameter, min.	22 mm	Protection degree	IP67
Seal insert	NBR	Tightening torque	11 Nm
Torque for cap nut, max.	16.5 Nm	Torque for cap nut, min.	15.5 Nm
Torque for connecting adapter, max.	11.5 Nm	Torque for connecting adapter, min.	10.5 Nm
Torque for lock nut, max.	11.5 N/m	Torque for lock nut, min.	10.5 N/m
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

VG PG36-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Plastic lock nuts, grey**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG36-K GR	Version
Order No.	1698240000	SKMU PA (plastic locknut), Locknut, PG 36, 8 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4008190884772	GF30)
Qty.	25 pc(s).	

Polyethylene flat gasket - GWDR PO

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG36-PO	Version
Order No.	1719510000	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 36,
GTIN (EAN)	4008190352776	Polyethylene
Qty.	50 pc(s).	

VG PG36-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG36-NP	Version
Order No.	1719610000	GWDR NP (flat gasket - neoprene), Sealing ring, PG 36, Neoprene
GTIN (EAN)	4008190352875	
Qty.	20 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1909830000](#)