

VG M25-1/K68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, M 25, 8 mm, OD min. 11 - OD max. 17 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	1909870000
Type	VG M25-1/K68
GTIN (EAN)	4032248536795
Qty.	50 pc(s).

VG M25-1/K68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	43 mm	Length (inches)	1.693 inch
Net weight	16.1 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (CSA)	115116
Certificate no. cable gland (GERMLLOYD)	E-14046	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260		

General information

AF size	29 mm	AF size 1	29 mm
Cable glands	metric	External thread	M 25
Halogen	Yes	Length of thread	8 mm
Material		Note: protection class	IP66 applications only possible with sealing ring for threaded connections. Without sealing ring for threaded connections, only IP54 is possible.
	Polyamide 6		
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	17 mm	Outer cable diameter, min.	11 mm
Pitch of thread	1.5 mm	Protection degree	IP67, IP68 - 5 bar (30 min.)
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Seal insert	CR
Standards	EN/IEC 62444	Tightening torque	3.5 Nm
Torque for cap nut, max.	5.5 Nm	Torque for cap nut, min.	4.5 Nm
Torque for connecting adapter, max.	4 Nm	Torque for connecting adapter, min.	3 Nm
Torque for lock nut, max.	4 N/m	Torque for lock nut, min.	3 N/m
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



ROHS

Conform

VG M25-1/K68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

VG M25-1/K68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Plastic lock nuts, grey**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M25 - K GR	Version
Order No.	1772470000	SKMU PA (plastic locknut), Locknut, M 25, 6 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4032248130214	GF30)
Qty.	100 pc(s).	

Polyethylene flat gasket - GWDR PO

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M25-PO	Version
Order No.	1777950000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 25, Polyethylene
GTIN (EAN)	4032248158218	
Qty.	50 pc(s).	

VG M25-1/K68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Neoprene flat gasket - GWDR NP**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M25-NP	Version
Order No.	1736250000	GWDR NP (flat gasket - neoprene), Sealing ring, M 25, Neoprene
GTIN (EAN)	4008190956042	
Qty.	100 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1909870000](#)