

IE-PS-SC-MM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



IE plug-in connectors, IP20, for copper and fibre optic cables

General ordering data

Version	FO connector, Plug SC, multimode, IP20
Order No.	1962910000
Type	IE-PS-SC-MM
GTIN (EAN)	4032248645107
Qty.	10 pc(s).

IE-PS-SC-MM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	12.4 g
------------	--------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Colour	Miscellaneous	Connection 1	SC-Simplex
Connection 2	gluing, crimping, polishing	Description of article	Plug SC, multimode
Fibre type	Multimode	Insertion loss	≤ 0.4 dB
Plugging cycles	1000	Protection degree	IP20
Return loss (attenuation)	≥ 30 dB		

General standards

Connector standard	IEC 61754-4
--------------------	-------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	GOST Approval
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1962910000](#)