

IE-PI-RJ45-FH-B-1.6**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

RJ45 plug-in connector (no tools required) according to IEC 60603-7-51.

General ordering data

Version	Substitute wire manager, Cat.6_A / Class E_A (ISO/IEC 11801 2010), EIA/TIA T568 B
Order No.	1992900000
Type	IE-PI-RJ45-FH-B-1.6
GTIN (EAN)	4050118378146
Qty.	30 pc(s).

IE-PI-RJ45-FH-B-1.6

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 4.233 g

Temperatures

Operating temperature -40 °C...85 °C

General data

Wiring	EIA/TIA T568 B	Speed	10 GBit
Insulation cross-section, min.	1.1	Insulation cross-section, max.	1.6
Category	Cat.6 _A / Class E _A (ISO/IEC 11801 2010)	Connection diameter, solid	0.51...0.64
Conductor connection cross-section, solid (AWG)	AWG 24...AWG 22	Connection diameter, flexible	0.46...0.76 mm
Conductor connection cross-section, flexible (AWG)	AWG 27...AWG 22	Conductor connection cross-section, extremely flexible	0.61...0.78 mm, Approval of the cable by Weidmüller necessary
Conductor connection cross-section, extremely flexible (AWG)	AWG 24...AWG 22, Approval of the cable by Weidmüller necessary	Note, very finely stranded line connection	Approval of the cable by Weidmüller necessary
Shielding	360°; shield contact	Protection degree	IP20
Ability to reconnect	≤ 4 cycles (with the same cross-section)		

Electrical properties

Contact resistance	≤ 20 mΩ	Current-carrying capacity at 50 °C	1 A
Dielectric strength, contact / contact	≥ 1000 V DC	Dielectric strength, contact / shield	≥ 1500 V DC
PoE / PoE+	conforming to IEEE 802.3at		

General standards

Certificate No. (cURus)	E471884	Certificate no. (cULus)	E471884
Connector standard	IEC 60603-7-5 1		

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90

Approvals

Approvals



ROHS	Conform
Certificate No. (cURus)	E471884
Certificate no. (cULus)	E471884

IE-PI-RJ45-FH-B-1.6

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Downloads

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[MB FREECONTACT EN](#)

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

[PI PROFINET CABLING EN](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1992900000](#)