

**PAC-UNIV-HE20-1:1-6M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

|            |                                                            |
|------------|------------------------------------------------------------|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">7789301060</a>                                 |
| Type       | PAC-UNIV-HE20-1:1-6M                                       |
| GTIN (EAN) | 8430243968829                                              |
| Qty.       | 1 pc(s).                                                   |

**PAC-UNIV-HE20-1:1-6M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 648 g |
|------------|-------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**General Data**

|                    |                                 |                       |                                 |
|--------------------|---------------------------------|-----------------------|---------------------------------|
| Cable              | Cable LiYY                      | Cable length          | 6 m                             |
| Connector PLC side | FLAT CABLE CONECTOR<br>HE10 20P | Interface connector   | FLAT CABLE CONECTOR<br>HE10 20P |
| Material           | PVC                             | Number of poles, min. | 20-pole                         |
| Outer diameter     | 8.6 ± 1 mm                      | Suitable for          | Digital signals                 |
| Wire cross-section | 0.25 mm <sup>2</sup>            |                       |                                 |

**Electrical Data**

|                        |                   |                                                |           |
|------------------------|-------------------|------------------------------------------------|-----------|
| Capacity wire / shield | 300 pF/m          | Capacity wire / wires                          | 300 pF/m  |
| High voltage test      | 1 kV/1s           | Permissible current strength per path,<br>max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac | Resistance                                     | ≤ 80 mΩ/m |
| Total current, max.    | 3 A               |                                                |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 |             |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789301060](#)