

FBCON TERM.D EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For applications in hazardous areas, PROFIBUS PA Ex junction boxes are available as 1-way, 2-way, 4-way, and 8-way distributors.

EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Protection class IP66
- Aluminium versions
- Profibus PA compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

Version	bus terminator without earth terminal, without clip-on foot, Terminator, IP66
Order No.	8606190000
Type	FBCON TERM.D EX
GTIN (EAN)	4032248274857
Qty.	1 pc(s).

FBCON TERM.D EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	36 mm	Height (inches)	1.417 inch
Width	45 mm	Width (inches)	1.772 inch
Length	49 mm	Length (inches)	1.929 inch
Net weight	178 g		

Temperatures

Storage temperature	-40 °C...80 °C	Ambient temperature	-40 °C...80 °C
Operating temperature	-40 °C...80 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical properties

Protection degree	IP66
-------------------	------

Technical data

Bus system	Profibus-DP, Modbus RS485	Cable entry	Brass cable gland
Conductor O.D.	-	Connection type PE	M16 cable gland
Type of distribution	Terminator	Type of mounting	surface-mounted
Colour	black	Protection degree	IP66
Type of mounting	surface-mounted		

Classifications

ETIM 6.0	EC001583	ETIM 7.0	EC001583
ETIM 8.0	EC001583	ECLASS 9.0	27-14-31-54
ECLASS 9.1	27-14-31-54	ECLASS 10.0	27-14-31-54
ECLASS 11.0	27-14-31-92		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E141197

Downloads



Approval/Certificate/Document of Conformity	Certification EAC Certification UL Declaration of Conformity.pdf
User Documentation	assembly instruction german / english Application-Guide-Planning and installing Fieldbus networks-using-FBCon_english_deutsch
Catalogues	Catalogues in PDF-format
Brochures	

FBCON TERM.D EX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8606190000](#)