

**ZDK 4-2 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

|            |                                                                                                              |
|------------|--------------------------------------------------------------------------------------------------------------|
| Version    | Feed-through terminal, Double-tier terminal, Tension-clamp connection, 4 mm <sup>2</sup> , 800 V, 32 A, blue |
| Order No.  | <a href="#">8670850000</a>                                                                                   |
| Type       | ZDK 4-2 BL                                                                                                   |
| GTIN (EAN) | 4032248423644                                                                                                |
| Qty.       | 50 pc(s).                                                                                                    |

**ZDK 4-2 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 60 mm      | Depth (inches) | 2.362 inch |
| Depth including DIN rail | 61 mm      | Height         | 77.6 mm    |
| Height (inches)          | 3.055 inch | Width          | 6.1 mm     |
| Width (inches)           | 0.24 inch  | Net weight     | 15.84 g    |

**Temperatures**

|                                  |                |                                  |     |
|----------------------------------|----------------|----------------------------------|-----|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 |
| Continuous operating temp., max. | 120            |                                  |     |

**Material data**

|                           |       |        |      |
|---------------------------|-------|--------|------|
| Material                  | Wemid | Colour | blue |
| UL 94 flammability rating | V-0   |        |      |

**System specifications**

|                                   |                                                                                  |                                     |     |
|-----------------------------------|----------------------------------------------------------------------------------|-------------------------------------|-----|
| Version                           | Tension-clamp connection, for plug-in cross-connector, One end without connector | End cover plate required            | Yes |
| Number of levels                  | 2                                                                                | Number of clamping points per level | 2   |
| Levels cross-connected internally | Yes                                                                              | PE connection                       | No  |
| Rail                              | TS 35                                                                            |                                     |     |

**Additional technical data**

|                          |         |            |       |
|--------------------------|---------|------------|-------|
| Explosion-tested version | No      | Open sides | right |
| Type of mounting         | Snap-on |            |       |

**CSA rating data**

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1236167 | Current size C (CSA)          | 30 A   |
| Voltage size C (CSA)          | 600 V          | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

**Conductors for clamping (rated connection)**

|                                                                                         |                      |                                                                                         |                          |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|--------------------------|
| Blade size                                                                              | 0.6 x 3.5 mm         | Clamping range, max.                                                                    | 6 mm <sup>2</sup>        |
| Clamping range, min.                                                                    | 0.13 mm <sup>2</sup> | Connection cross-section, finely stranded, max.                                         | 6 mm <sup>2</sup>        |
| Connection cross-section, finely stranded, min.                                         | 0.5 mm <sup>2</sup>  | Connection direction                                                                    | Inclined / angled        |
| Gauge to IEC 60947-1                                                                    | A3                   | Number of connections                                                                   | 4                        |
| Stripping length                                                                        | 10 mm                | Twin wire-end ferrules, max.                                                            | 1.5 mm <sup>2</sup>      |
| Twin wire-end ferrules, min.                                                            | 0.5 mm <sup>2</sup>  | Type of connection                                                                      | Tension-clamp connection |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>      |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>    | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>      |
| Wire connection cross-section, solid core, max.                                         | 6 mm <sup>2</sup>    | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup>      |

## ZDK 4-2 BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## General

|      |       |           |               |
|------|-------|-----------|---------------|
| Rail | TS 35 | Standards | IEC 60947-7-1 |
|------|-------|-----------|---------------|

## Rating data

|                                 |                   |                                              |        |
|---------------------------------|-------------------|----------------------------------------------|--------|
| Rated cross-section             | 4 mm <sup>2</sup> | Rated voltage                                | 800 V  |
| Rated current                   | 32 A              | Current at maximum wires                     | 32 A   |
| Standards                       | IEC 60947-7-1     | Volume resistance according to IEC 60947-7-x | 1 mΩ   |
| Rated impulse withstand voltage | 8 kV              | Power loss in accordance with IEC 60947-7-x  | 1.02 W |
| Pollution severity              | 3                 |                                              |        |

## UL rating data

|                                         |        |                                         |        |
|-----------------------------------------|--------|-----------------------------------------|--------|
| Certificate No. (UR)                    | E60693 | Conductor size Factory wiring max. (UR) | 10 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Field wiring max. (UR)   | 10 AWG |
| Conductor size Field wiring min. (UR)   | 26 AWG | Current size C (UR)                     | 25 A   |
| Voltage size C (UR)                     | 600 V  |                                         |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ECLASS 9.0  | 27-14-11-20 |
| ECLASS 9.1  | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 |             |             |

## Approvals

Approvals



|                       |         |
|-----------------------|---------|
| ROHS                  | Conform |
| UL File Number Search | E60693  |

## Downloads

|                                             |                                                                                                                                            |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">EAC certificate</a><br><a href="#">Declaration of Conformity</a><br><a href="#">CE Declaration of Conformity all terminals</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                            |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                                                                   |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>                                                                                            |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                   |
| Brochures                                   |                                                                                                                                            |

### ZDK 4-2 BL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

## ZDK 4-2 BL

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

4 mm<sup>2</sup>


End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

|            |                            |                                      |
|------------|----------------------------|--------------------------------------|
| Type       | ZAP ZDK 4-2 OR             | Version                              |
| Order No.  | <a href="#">8704430000</a> | Z-series, End plate                  |
| GTIN (EAN) | 4032248375394              |                                      |
| Qty.       | 50 pc(s).                  |                                      |
| Type       | ZAP/TW ZDK4-2              | Version                              |
| Order No.  | <a href="#">8670760000</a> | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4032248337415              |                                      |
| Qty.       | 50 pc(s).                  |                                      |

## Z-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data


|            |                            |                       |
|------------|----------------------------|-----------------------|
| Type       | ZEW 35                     | Version               |
| Order No.  | <a href="#">9540000000</a> | Z-series, End bracket |
| GTIN (EAN) | 4008190956264              |                       |
| Qty.       | 20 pc(s).                  |                       |

**ZDK 4-2 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Z-Series**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

|            |                            |                                   |
|------------|----------------------------|-----------------------------------|
| Type       | ZTA 6/ZA                   | Version                           |
| Order No.  | <a href="#">1780660000</a> | Accessories, Test adapter, 17.5 A |
| GTIN (EAN) | 4032248180189              |                                   |
| Qty.       | 25 pc(s).                  |                                   |

**Z-Series**

Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

**General ordering data**

|            |                            |                 |
|------------|----------------------------|-----------------|
| Type       | ZAD 1/4                    | Version         |
| Order No.  | <a href="#">1609110000</a> | Z-series, Cover |
| GTIN (EAN) | 4008190190910              |                 |
| Qty.       | 20 pc(s).                  |                 |

## ZDK 4-2 BL

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

4 mm<sup>2</sup>

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | ZQV 4/3 GE                 | Version                                                           |
| Order No.  | <a href="#">1608960000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263232              |                                                                   |
| Qty.       | 60 pc(s).                  |                                                                   |
| Type       | ZQV 4/5 GE                 | Version                                                           |
| Order No.  | <a href="#">1608980000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263256              |                                                                   |
| Qty.       | 20 pc(s).                  |                                                                   |
| Type       | ZQV 4/9 GE                 | Version                                                           |
| Order No.  | <a href="#">1609020000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263294              |                                                                   |
| Qty.       | 20 pc(s).                  |                                                                   |
| Type       | ZQV 4/2 GE                 | Version                                                           |
| Order No.  | <a href="#">1608950000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263225              |                                                                   |
| Qty.       | 60 pc(s).                  |                                                                   |
| Type       | ZQV 4/10 GE                | Version                                                           |
| Order No.  | <a href="#">1609030000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263300              |                                                                   |
| Qty.       | 20 pc(s).                  |                                                                   |
| Type       | ZQV 4/20 GE                | Version                                                           |
| Order No.  | <a href="#">1909010000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 20 |
| GTIN (EAN) | 4032248535637              |                                                                   |
| Qty.       | 20 pc(s).                  |                                                                   |
| Type       | ZQV 4/6 GE                 | Version                                                           |
| Order No.  | <a href="#">1608990000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263263              |                                                                   |
| Qty.       | 20 pc(s).                  |                                                                   |
| Type       | ZQV 4/4 GE                 | Version                                                           |
| Order No.  | <a href="#">1608970000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263249              |                                                                   |
| Qty.       | 60 pc(s).                  |                                                                   |
| Type       | ZQV 4/8 GE                 | Version                                                           |
| Order No.  | <a href="#">1609010000</a> | Accessories, Cross-connector, 32 A                                |
| GTIN (EAN) | 4008190263287              |                                                                   |
| Qty.       | 20 pc(s).                  |                                                                   |

## ZDK 4-2 BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Accessories

|            |                            |                                    |
|------------|----------------------------|------------------------------------|
| Type       | ZQV 4/7 GE                 | Version                            |
| Order No.  | <a href="#">1609000000</a> | Accessories, Cross-connector, 32 A |
| GTIN (EAN) | 4008190263270              |                                    |
| Qty.       | 20 pc(s).                  |                                    |

## Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

## General ordering data

|            |                            |                                                                     |
|------------|----------------------------|---------------------------------------------------------------------|
| Type       | SDIS SLIM 0.6X3.5X100      | Version                                                             |
| Order No.  | <a href="#">2749610000</a> | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118896350              | thickness (A): 0.6 mm                                               |
| Qty.       | 1 pc(s).                   |                                                                     |

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/6 MC SDR             | Version                                                   |
| Order No.  | <a href="#">1609830000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4008190456603              | Weidmueller, To customer specification                    |
| Qty.       | 200 pc(s).                 |                                                           |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8670850000](#)