

M-D-STRIPAX LWL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- With 1 mm diameter inner conductor
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9003750000
Type	M-D-STRIPAX LWL
GTIN (EAN)	4008 190068042
Qty.	1 pc(s).

M-D-STRIPAX LWL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	16 mm	Depth (inches)	0.63 inch
Height	135 mm	Height (inches)	5.315 inch
Width	82 mm	Width (inches)	3.228 inch
Weight	110 g	Net weight	96.73 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Description of article	Stripping tool for fibre-optic cables
------------------------	---------------------------------------

Stripping tools

Cable type	POF conductor with an inner conductor of 1 mm	Colour	grey
Max. conductor diameter	1 mm	Stripping length, max.	7.5 mm

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ECLASS 9.0	21-04-37-06
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-37-06
ECLASS 11.0	21-04-37-06		

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

M-D-STRIPAX LWL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories / replacement parts**

- With 1 mm diameter inner conductor
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping

General ordering data

Type	MEHA KP LWL M-D-SPX	Version
Order No.	9003760000	Accessories, Spare cutting blade
GTIN (EAN)	4008190055110	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9003750000](#)