

CRIMPER 6 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for contacts, 0.5mm ² , 6mm ²
Order No.	9040530000
Type	CRIMPER 6 Z
GTIN (EAN)	4008190461102
Qty.	1 pc(s).

CRIMPER 6 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	30 mm	Depth (inches)	1.181 inch
Height	78 mm	Height (inches)	3.071 inch
Width	200 mm	Width (inches)	7.874 inch
Weight	446 g	Net weight	377.61 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Description of article	Crimping tool for wire-end ferrules 0,5 - 6mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Crimping range, max.	6 mm ²	Crimping range, min.	0.5 mm ²
Type of contact	Wire-end ferrules with/without plastic collars		

tool data crimping

Crimping profile 1, max.	0.5 mm ²	Crimping profile 1, min.	0.25 mm ²
Crimping profile 2, max.	1.5 mm ²	Crimping profile 2, min.	0.75 mm ²
Crimping profile 3, max.	2.5 mm ²	Crimping profile 4, max.	4 mm ²
Crimping profile 5	6 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11		

Approvals

Approvals

**Downloads**

Catalogues	Catalogues in PDF-format
------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9040530000](#)