



General ordering data

Order No.	1925583000
Part designation	SAIL-M12BG-4-30V
Version	Sensor/Actuator line, One end without connector, LED: No, 30.00 m, PVC/PVC
EAN	4032248652174
Qty.	1 pc(s).

Technical data

Ambient temperature, max.	80 °C
Ambient temperature, min.	-30 °C
Cable diameter, max.	5.5 mm
Cable diameter, min	5.1 mm
Connection cross-section	0,34
Contact material	Ni/Au
Contact surface	gold-plated
Contact tube diameter	M12
Core cross-section	0.34 mm ²
Material	PVC/PVC
Protection class	IP 67
Rated current	4 A
Rated voltage	250 V DC / 300 V AC
Sheathing colour	black
No. of poles	4
Version	Female socket, straight
Cable length	30 m

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000304
ETIM 3.0	EC001855
eClass 4.1	27-06-00-00
eClass 5.0	27-06-91-90
eClass 5.1	27-06-91-90

Similar products

Order No.	Part designation	Version
1925580150	SAIL-M12BG-4-1.5V	Sensor/Actuator line, One end without connector, LED: No, 1.50 m, PVC/PVC
1925581000	SAIL-M12BG-4-10V	Sensor/Actuator line, One end without connector, LED: No, 10.00 m, PVC/PVC
1925581500	SAIL-M12BG-4-15V	Sensor/Actuator line, One end without connector, LED: No, 15.00 m, PVC/PVC
1925580200	SAIL-M12BG-4-2.0V	Sensor/Actuator line, One end without connector, LED: No, 2.00 m, PVC/PVC
1925582000	SAIL-M12BG-4-20V	Sensor/Actuator line, One end without connector, LED: No, 20.00 m, PVC/PVC
1925582500	SAIL-M12BG-4-25V	Sensor/Actuator line, One end without connector, LED: No, 25.00 m, PVC/PVC
1925580300	SAIL-M12BG-4-3.0V	Sensor/Actuator line, One end without connector, LED: No, 3.00 m, PVC/PVC
1925580500	SAIL-M12BG-4-5.0V	Sensor/Actuator line, One end without connector, LED: No, 5.00 m, PVC/PVC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1925583000](#)