



General ordering data

Order No.	9457690060
Part designation	SAIL-M12BW-5-0.6U
Version	Sensor/Actuator line, One end without connector, LED: No, 0.60 m, PUR/PVC
EAN	4032248229000
Qty.	1 pc(s).

Technical data

Ambient temperature, max.	80 °C
Ambient temperature, min.	-30 °C
Cable diameter, max.	5.8 mm
Cable diameter, min	5.4 mm
Connection cross-section	0.34
Contact material	Ni/Au
Contact surface	gold-plated
Contact tube diameter	M12
Core cross-section	0.34 mm ²
Material	PUR/PVC
Protection class	IP 67
Rated current	4 A
Rated voltage	125 V
Sheathing colour	black
Wiring diagram	
No. of poles	5
Version	bush, 90°
Cable length	0.6 m

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000304
ETIM 3.0	EC001855
eClass 4.1	27-06-00-00
eClass 5.0	27-06-91-90
eClass 5.1	27-06-91-90

Similar products

Order No.	Part designation	Version
9457690030	SAIL-M12BW-5-0.3U	Sensor/Actuator line, One end without connector, LED: No, 0.30 m, PUR/PVC
9457690090	SAIL-M12BW-5-0.9U	Sensor/Actuator line, One end without connector, LED: No, 0.90 m, PUR/PVC
9457690120	SAIL-M12BW-5-1.2U	Sensor/Actuator line, One end without connector, LED: No, 1.20 m, PUR/PVC
9457690150	SAIL-M12BW-5-1.5U	Sensor/Actuator line, One end without connector, LED: No, 1.50 m, PUR/PVC
9457691000	SAIL-M12BW-5-10U	Sensor/Actuator line, One end without connector, LED: No, 10.00 m, PUR/PVC
9457690200	SAIL-M12BW-5-2.0U	Sensor/Actuator line, One end without connector, LED: No, 2.00 m, PUR/PVC
9457690250	SAIL-M12BW-5-2.5U	Sensor/Actuator line, One end without connector, LED: No, 2.50 m, PUR/PVC
9457690300	SAIL-M12BW-5-3.0U	Sensor/Actuator line, One end without connector, LED: No, 3.00 m, PUR/PVC
9457913000	SAIL-M12BG-5-30U	
9457914500	SAIL-M12BG-5-45U	
9457690500	SAIL-M12BW-5-5.0U	Sensor/Actuator line, One end without connector, LED: No, 5.00 m, PUR/PVC
9457690800	SAIL-M12BW-5-8.0U	
9457918500	SAIL-M12BG-5-85U	
1883462000	SAIL-M12BW-8-20U	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9457690060](#)