

PAC
PAC-UNIV-D25M-D25M-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

Cable pre-confeccionado sub-d según IEC-807/
DIN41652

- Sub-d a Sub-d
- Sub-d a punteras
- Cable apantallado

General ordering data

Type	PAC-UNIV-D25M-D25M-3M
Order No.	1349800030
Version	Pre-assembled cable, PAC, Cable LiYCY, 10.15 ± 1 mm
GTIN (EAN)	4032248242733
Qty.	1 pc(s).

PAC

PAC-UNIV-D25M-D25M-3M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight	577 g
------------	-------

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General Data

Connector PLC side	SUB-D MALE 25P	Interface connector	SUB-D MALE 25P
Number of poles, min.	25-pole	Outer diameter	10.15 ± 1 mm
Cable	Cable LiYCY	Cable length	3 m
Material	PVC	Wire cross-section	0.25 mm ²

Electrical Data

Rated voltage (text)	≤ 60 Vdc ≤ 25 Vac	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	≤ 80 mΩ/m

Classifications

ETIM 5.0	EC000237	ETIM 6.0	EC000237
eClass 6.2	27-24-92-05	eClass 7.1	27-24-92-05
eClass 8.1	27-24-92-05	eClass 9.0	27-24-22-20
eClass 9.1	27-24-22-20		

Approvals

ROHS	Conform
------	---------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1349800030](#)