

A-series
ZQV 2.5N/10 RD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	ZQV 2.5N/ 10 RD
Order No.	2108910000
GTIN (EAN)	4050118486018
Qty.	20 pc(s).

A-series
ZQV 2.5N/10 RD
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Width	48.7 mm	Width (inches)	1.917 inch
Height	24.7 mm	Height (inches)	0.972 inch
Depth	2.8 mm	Depth (inches)	0.11 inch
Net weight	5.83 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Wemid	Colour	red
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
Type of mounting	Direct mounting		

Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	eClass 6.2	27-14-11-40
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	2434520000_BED-ANL.ZQV_A_REIHE.pdf

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2108910000](#)