

PAC
PAC-C300-32-F-50-1M**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

The pre-wired cables allow connecting the Honeywell C300 IOTAs (Input Output Terminal Assemblies) and the Weidmüller FTAs (Field Terminal Assemblies) in a manner that is quick, simple and error free.

The cables may be delivered with single or dual connectors, or even with free ends and end ferrules.

The hood makes it easier to handle and it offers a robust connection with the IOTA. It also allows using cables of different gauge sizes and lengths of up to 50m.

General ordering data

| | |
|------------|---|
| Type | PAC-C300-32-F-50-1M |
| Order No. | 1373940010 |
| Version | Pre-assembled cable, PAC, Cable LiYCY, 0.50 mm ² |
| GTIN (EAN) | 4032248258390 |
| Qty. | 1 pc(s). |

Data sheet

PAC PAC-C300-32-F-50-1M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|-------|
| Net weight | 431 g |
|------------|-------|

Temperatures

| | | | |
|-----------------------------|-------------|-----------------------------|-------------|
| Operating temperature, max. | 50 °C | Operating temperature, min. | -10 °C |
| Storage temperature, max. | 60 °C | Storage temperature, min. | -10 °C |
| Operating temperature | -10...50 °C | Storage temperature | -10...60 °C |

General Data

| | | | |
|-----------------------|---|---------------------|-----------------------------|
| Connector PLC side | H0.50/10 (FERRULES 0.50mm ²) | Interface connector | 2 x BLC 5.08/16/180BR BK |
| Number of poles, min. | 32-pole | Outer diameter | 15,75 ± 1 mm |
| Cable | Cable LiYCY | Cable length | 1 m |
| Material | PVC | Wire cross-section | 0.5 mm ² |

Electrical Data

| | | | |
|----------------------|---------------------|--|-----------|
| Rated voltage (text) | ≤ 250 Vdc ≤ 250 Vac | Permissible current strength per path, max. | 1 A |
| Total current, max. | 7 A | Resistance | ≤ 39 mΩ/m |
| High voltage test | 1 KV/1s | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 4.0 | EC000237 | ETIM 5.0 | EC000237 |
| ETIM 6.0 | EC000237 | eClass 6.2 | 27-24-92-05 |
| eClass 7.1 | 27-24-92-05 | eClass 9.0 | 27-24-22-20 |
| eClass 9.1 | 27-24-22-20 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 4.5 ELECTR 16/17 EN |
| User Documentation | Colours chart |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1373940010](#)