

**PAC**  
**PAC-S300-RV36-V0-1M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |                                                            |
|------------|------------------------------------------------------------|
| Type       | PAC-S300-RV36-V0-1M5                                       |
| Order No.  | <a href="#">7789215015</a>                                 |
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| GTIN (EAN) | 8430243964289                                              |
| Qty.       | 1 pc(s).                                                   |

# PAC

## PAC-S300-RV36-V0-1M5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Temperatures

|                             |             |                             |             |
|-----------------------------|-------------|-----------------------------|-------------|
| Operating temperature, max. | 50 °C       | Operating temperature, min. | -10 °C      |
| Storage temperature, max.   | 60 °C       | Storage temperature, min.   | -10 °C      |
| Operating temperature       | -10...50 °C | Storage temperature         | -10...60 °C |

### General Data

|                       |                                            |                     |                             |
|-----------------------|--------------------------------------------|---------------------|-----------------------------|
| Connector PLC side    | SIEMENS S7300<br>6ES7921-3AH20-1AA0<br>40P | Interface connector | WEIDMUELLER RSV 36P<br>MALE |
| Number of poles, min. | 36-pole                                    | Outer diameter      | 11.2 ± 1 mm                 |
| Cable                 | Cable LiYY                                 | Cable length        | 1.5 m                       |
| Material              | PVC                                        | Wire cross-section  | 0.25 mm <sup>2</sup>        |

### Electrical Data

|                      |                     |                                             |           |
|----------------------|---------------------|---------------------------------------------|-----------|
| Rated voltage (text) | ≤ 250 Vdc ≤ 250 Vac | Permissible current strength per path, max. | 1 A       |
| Total current, max.  | 3 A                 | Resistance                                  | ≤ 80 mΩ/m |
| High voltage test    | 1 KV/1s             |                                             |           |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC000237    | ETIM 6.0   | EC000237    |
| eClass 7.1 | 27-24-92-05 | eClass 8.1 | 27-24-92-05 |
| eClass 9.0 | 27-24-22-20 | eClass 9.1 | 27-24-22-20 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789215015](#)