



Datasheet for part number TR1208PFS1NB

Our Catalog Part Number: TR1208PFS1NB
Our Global Manufacturing Part Number: 192926-0510
Brand: Cannon Product Category: Trident Product Line: Trident Series: TR

Product Datasheet	
Series	Trident Ringlock
Operating Voltage	Up to 250 V ac rms Up to 380 Vac rms (Size 1807 only)
Contact Current Rating	Up to 13 A
Operating Temperature	-55°C to +105°C
Insulation Resistance	5000 Megaohms at 500 V dc
Durability	Up to 500 Mating Cycles
Sealing	Up to IP65
Flammability Rating	UL94-V0
Materials and Finishes	Connector Body: Black Nylon Coupling Ring: Nickel Plated Copper Alloy Bayonet Pins: Stainless Steel Bayonet Pins Support Band: Nickel Plated Copper Alloy
Shell Size	12
Number of Contacts	08
Type	Plug
Contact Type	Accepts Female Contacts
Mounting Style	Standard
Material	Nylon
Colour	Black

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ITT Cannon:](#)

[TR1208PFS1NB](#)