



[Home](#) | [Sign In](#) | [Contact Us](#)

SEARCH

Go



Standard D (Stamped)

PART NUMBER: ZDBE25P-OL2-146



Image Disclaimer:

Please use Customer Drawing for design activity: line art and other pictures are general representations of product dimensions.

[View Line Drawings](#)

Where Sold	Americas, Asia Pacific, Europe
Product Group	D-Subminiature
Product Sub-Family	D-Sub Standard
Component Type	Connector
Application Type	Commercial
Cable or PC Board	PC Board
Gender	Plug
Number of Signal Pins	25
Number of Size 8 contacts	0
Straight or Right Angle	Straight
Contact Plating	Gold over Nickel
Shell Plating	Tin (with Grounding Dimples)



- ☒ [Sales Support](#)
- ☒ [Ask a Specialist](#)
- ☒ [Product Home](#)
- ☒ [Stock Check](#)

PRINTABLE PAGE

Hardware	4-40 Standoffs, Boardlocks
Other Features	Stamped Contacts
Contact Termination	0,64 (.025) sq, 3,18 (.125) Extention
Shell Size	DB
Temperature Rating	-55°C to +105°C
Current Capacity	5 A
Contact Resistance	15 milli ohms max.
Dielectric Withstanding Voltage	1000 V AC at Sea Level
Insulator Material	Thermoplastic, UL 94V-0
Contact Material	Copper Alloy
Shell Material	Steel
Hardware Material and Plating	Steel, Tin Plated



☐ [Home](#)|[About ITT](#)|[Products](#)|[Design Center](#)|[Literature](#)|[News & Events](#)|[Search Tools](#)|[Global Sales Support](#)
© *ITT Corporation. All rights reserved.* [Legal Disclaimer](#)|[Privacy Policy](#)|[General Terms of Sale](#)
[Channel Partners Sign-In](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ITT Cannon:](#)

[ZDBE25POL2-146](#)