


SPECIFICATION
Current Rating:3.0 Amp
Withstand Voltage:500V AC/DC
Insulator Resistance:1000 Megaohms Min.
Contact Resistance:20 Milliohms Max.
Operation Temperature:-40°C~+105°C
Contact:Brass,Gold Plated Over Nickel
⚠ Insulator:PA6T+30%G.F(UL94V-0),Black
RoHS Compliant

4UCON 元化興業股份有限公司
4UCON TECHNOLOGY INC.

DRAWING No. 00527		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.40 .XX ±0.25 .XXX ±0.15 ANG. ±3'						
		EMILY								
		CHECKED BY								
		HZF								
DRAWING BY		SONG				⚠ A1	Modify Data		HZF	07/28/2011
						⚠ A0	NEW RELEASE		HZF	09/05/2008
SCALE	NONE	REV.	A1	UNIT		NO.	REV.	REVISIONS	CHK	DATE
	5		6		7		8		9	0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Gravitech:

8Fx1-254mm