

BGA Heat Sink (High Aspect Ratio Ext.) Standard Pin Fin



ATS Part#:	ATS048054010-PF034
Description:	53.30 x 47.20 x 10.20 mm BGA Heat Sink (High Aspect Ratio Ext.) Standard Pin Fin
Heat Sink Type:	Standard Pin Fin
Heat Sink Attachment:	N/A
Equivalent Part Number:	N/A



*Image above is for illustration purpose only.


Features & Benefits

- Excellent balance of low cost and high performance in an aluminum heat sink.
- Designed for semiconductor devices with omni-directional airflow requirements.
- 11 x 11 pin array
- Available with a variety of thermal adhesive tape options. Contact sales@qats.com for product configurations.

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	7 °C/W	N/A °C/W	N/A °C/W	N/A °C/W	N/A °C/W	N/A °C/W	N/A °C/W
	Ducted Flow	0	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	53.30 mm	47.20 mm	10.20 mm	N/A mm	NO TIM	Black Anodized
<p>Notes:</p> <ul style="list-style-type: none">• Dimension A and B refer to component size.• Dimension C is the heat sink height from the bottom of the base to the top of the fin field.• Thermal performance data are provided for reference only. Actual performance may vary by application.• ATS reserves the right to update or change its products without notice to improve the design or performance.• ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant.• Contact ATS to learn about custom options available.						

*Image above is for illustration purpose only.

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Thermal Solutions:](#)

[ATS048054010-PF034](#)