






	H	K0	T	X	①
A	4.3	5.3	0.4	1500	
B	5	6.6	0.5	1250	

FORCE (gf)		Knob Color
1	180 ± 50	NATURAL(NK)
3	250 ± 50	BLACK(BK)
4	230 ± 30	NATURAL(NK)



TOTAL X PCS PER REEL. ①




示意图 SCHEMATIC

安装孔 PIERCING PLAN

规格 Specifications

额定负荷 Ratings	DC 12 V 50 m A
初期接触电阻 Initial Contact Resistance	100 mΩ Max.
绝缘电阻 Insulation Resistance	DC100 V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric Voltage	AC 250 V (50~60HZ) 60 Sec.

负荷寿命 Operating Life With Load	操作力见上表
	30,000 次 Cycles

5	端子 TERMINAL	C2680R	2	Ag PLATED				
4	弹片 SPRING PLATE	SUS	1	Ag CLAD	A03	增加操作力规格, 见标示 ⑥	彭云军	2008.1.24
3	盖片 COVER	SUS	1	NATURAL	A02	TOTAL 1250PCS PER REEL. 变更为TOTAL X PCS PER REEL; 6.6变更为K0; 0.5变更为T; 增加K0值尺寸、T值尺寸、X值数量, 见标注 ①	鲁 腾	2007-05-15
2	胶柄 KNOB	PA	1	见上表	A01		刘红梅	2006-10-27
1	胶壳 HOUSING	PA	1	BLACK C	标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
序NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS	DWG NO. ITEM2773			

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	TACT SWITCH		ITEM NO	RS-032G05__-SM RT		
UNDER 1	± 0.10	DRAWN	彭云军	2008.1.24	VERSION	A03	PAGE 1	OF 1
1 - 10	± 0.30	REVIEWED	张念明	2008.1.25	SCALE		UNIT	mm
OVER 10	± 0.50	APPROVED	程先金	2008.1.25	PROJECTION			

COMAX ELECTRONICS (HUIZHOU) CO., LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[RS-032G05A3-SM RT](#) [RS032G05A3SMRT](#)