

LCS Series

Subminiature Sealed Snap-acting Switches



Features/Benefits

- **Compact design**
- **Long life and high electrical capacity**
- **Quick connect, solder terminals, PC terminals, wire leads**
- **Wide variety of actuator styles**
- **RoHS compatible, RoHS compliant**
- **IP67**

Typical Applications

- ***Motorized equipment***
- ***Sump pump***
- ***Thermostatic controls***
- ***Computers***
- ***Air conditioners***



Specifications

CONTACT RATING: 6 AMP, 250 V AC and
5 AMP, 125/250 V AC
0.1 AMP, 125/250 V AC

ELECTRICAL LIFE: 10,000 cycles

INSULATION RESISTANCE: 100 M ohm min.

DIELECTRIC STRENGTH: 1,000 VAC

OPERATING TEMPERATURE:

-40°C to +120°C (without wire)

-40°C to +85°C (with UL1007 wire)

-40°C to +105°C (with UL1015 wire)

-40°C to +105°C (with UL1430 wire)

-40°C to +80°C (with UL1061 wire)

-40°C to +120°C (with UL1330 wire)

OPERATING FORCE: (see ACTUATOR'S option sections).

MOUNTING: 2-56 screws, torque 2.3 in/lbs max.

NOTE: Specifications and materials listed above are for switches with standard options.
For information on specific and custom switches, consult Customer Service center.

Materials

SWITCH HOUSING: Thermoplastic polyester or high temperature thermoplastic (PTS) (UL 94V-0).

ACTUATOR BUTTON: Thermoplastic polyester.

SPRING: Copper alloy.

PIVOT: Copper alloy.

MOVABLE CONTACTS: Silver nickel


STATIONARY CONTACTS: Silver nickel on copper alloy.

TERMINALS: Copper alloy.

ACTUATOR LEVEL: Stainless steel.


Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages J-27 thru J-29. For additional options not shown in catalog, consult Customer Service Center.



Dimensions are shown: mm
Specifications and dimensions subject to change

SERIES



ELECTRICAL RATING

RoHS COMPLIANT *	RoHS COMPATIBLE *	OPTION CODE	ELECTRICAL RATING
YES	YES	05	5 AMP, 125/250 V AC 6 AMP, 250 V AC
YES	YES	01	0.1 AMP, 125/250 V AC

OPERATING FORCE

OPTION CODE	OPERATING FORCES (grams)
1	150 g. max.
2	203 g. max.




www.ck-components.com

LCS Series


Subminiature Sealed Snap-acting Switches

ACTUATOR 


P00




T19




T07




A05




T00




T28




T13




S26







T05



T43



Snap-acting



ACTUATOR OPTION CODE	A LENGTH OF LEVER	B OVER TRAVEL (MIN)	C PRE TRAVEL (MAX)	D OPERATING POSITION	E FREE POSITION (MAX)	DIFFERENTIAL MOTION (MAX)		OPERATING FORCE (MIN)		RELEASE FORCE (MIN)	
						150	203	150	203	150	203
P00	N/A	0.6	1.2	8.4 ± 3	9.9	0.2	0.2	150	203	30	50
T00	11.9	0.6	3.2	8.8 ± 9	11.1	0.5	0.5	66	98	10	21
T05	17.40	0.9	4.3	8.8 ± 1.1	12	0.6	0.6	73	82	14	16
T07	19.40	1	4.8	8.8 ± 1.2	12.4	0.7	0.7	55	66	11	13
T13	25.5	1.6	6.3	8.8 ± 1.6	13.5	0.9	0.9	29	54	6	11
T19	33.3	1.95	8	8.8 ± 2.0	15	1.75	1.75	32	40	2	5
T28	40.7	2.1	10.1	8.8 ± 2.6	16.3	2.3	2.3	33	39	1	8
T43	55.9	2.9	13.8	8.8 ± 3.5	19.1	3.6	3.6	23	33	1	7
S26	18.6	1	4.6	10.7 ± 1.2	14.1	0.65	0.65	42	68	7	14
A05	17.20	0.9	4.3	14.5 ± 1.1	17.7	0.6	0.6	60	72	12	15



Third Angle
Projection


Dimensions are shown: mm
Specifications and dimensions subject to change

C&K


LCS Series Subminiature Sealed Snap-acting Switches

TERMINATIONS


S SOLDER




Q QUICK CONNECT 2.8mm / 0.110"




P PC THRU HOLE




Z or W "A" WIRE ORIENTATION




Z or W "B" WIRE ORIENTATION "Y" OR "W" CIRCUITRY




Z or W "C" WIRE ORIENTATION "Y" OR "W" CIRCUITRY



Z or W "B" WIRE ORIENTATION "C" CIRCUITRY



Z or W "C" WIRE ORIENTATION "C" CIRCUITRY



CIRCUITRY

- C** SPDT (Single Pole, Double Throw)
- W** SPST N.C. (Single Pole, Single Throw, Normally Closed)
- Y** SPST N.O. (Single Pole, Single Throw, Normally Open)



Third Angle
Projection

Dimensions are shown: mm
Specifications and dimensions subject to change



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[LCS052T05WB22AC](#) [LCS052A05ZA20DW](#) [LCS052P00WA20CC](#) [LCS052T13WC20BY](#) [LCS052T28WB20AY](#)
[LCS052P00WA20AY](#) [LCS052P00WA20AC](#) [LCS052T07WC20CC](#) [LCS052S26WA20BY](#) [LCS052S26WC20AW](#)
[LCS052T28ZB20AY](#) [LCS052T00WA20BC](#) [LCS052S26ZA20DW](#) [LCS052S26WA20BC](#) [LCS052T05WC20AW](#)
[LCS052A05WC22AW](#) [LCS012T07WA22AY](#) [LCS052T00WA20BY](#) [LCS052S26ZA20DY](#) [LCS012T05WA20AW](#)
[LCS052A05ZA20DY](#) [LCS052P00WA24AC](#) [LCS052T13WA20BY](#) [LCS052T05WB22AW](#) [LCS052T07WA20BY](#)