


DDS Series

Micro Mini Thru-hole Detect Switches



Features/Benefits

- Vertical or horizontal actuation
- 2mm overtravel—Ideal for detector applications
- Low actuations force (less than 40 grams)
- RoHS compliant and compatible

Typical Applications

- Detect the presence of a mechanical device
- Medical devices
- Consumer electronic devices

Specifications

CONTACT RATING: 0.1A @ 30 VDC.

MECHANICAL & ELECTRICAL LIFE: 50,000 cycles.

CONTACT RESISTANCE: 150 m Ω max. initial.

INSULATION RESISTANCE: 100 M Ω min. @ 100 VDC.

OPERATING TEMPERATURE: -40°C to +85°C.

DIELECTRIC STRENGTH: 100 volts AC @ 60 Hz.

PACKAGING: Bulk.

Materials

HOUSING: P.P.S.


ACTUATOR: PA66

MOVABLE CONTACT: Tin bronze, silver plated.


NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

How To Order


Complete part numbers for DDS Series Switches are shown below.



DDS001
SPST



PC MOUNTING





PART NUMBER	DESCRIPTION	SCHEMATIC
DDS001	Vertical Actuator	SPST N.O.



Dimensions are shown: mm
Specifications and dimensions subject to change



DDS Series Micro Mini Thru-hole Detect Switches

PART NUMBER	DESCRIPTION	SCHEMATIC
DDS002	Right angle, actuator right	 SPST N.O.



DDS002
SPST


PART NUMBER	DESCRIPTION	SCHEMATIC
DDS003	Right angle, actuator left	 SPST N.O.



DDS003
SPST



Detect




Dimensions are shown: mm
Specifications and dimensions subject to change

DDS Series Micro Mini Thru-hole Detect Switches



DDS004
SPST



PART NUMBER	DESCRIPTION	SCHEMATIC
DDS004	Vertical actuator	 SPST N.O.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[DDS001](#) [DDS002](#) [DDS003](#)