


FDSD Series Micro Mini Side Actuated Detect Switches

NEW



Features/Benefits

- Extremely small package size
- Vertical Side Actuation
- Flat or Bending Terminations
- Long Travel Type
- RoHS Compatible and Compliant

Typical Applications

- Consumer electronics
- Medical devices
- Safety control devices

Specifications


CONTACT RATING: 50 μ A @ 3VDC, 10 mA @ 5 VDC
 MECHANICAL & ELECTRICAL LIFE: 50,000 operations
 CONTACT RESISTANCE: 1 Ω max
 INSULATION RESISTANCE: 100M Ω min
 DIELECTRIC STRENGTH: 100VAC @ 1 minute
 OPERATING TEMPERATURE: -40°C to +85°C
 OPERATING FORCE: 40gf max.
 TRAVEL: 3.05 mm or 60°
 SOLDERABILITY: According to lead free solder profiles
 PACKAGING: 3,500 pieces per reel.

Materials

BASE: PA9T
 COVER: C7701R
 ACTUATOR: PA 46
 MOVABLE CONTACT: Beryllium Copper
 TERMINALS: Phosphor Bronze, Ag over Ni Plating

Build-A-Switch

Complete part numbers for FDSD Series are shown below.





E

Detect



FDSD Series Micro Mini Side Actuated Detect Switches

SERIES



FDSD001R



FDSD002R



TAPE & REEL



SECTION A-A

C&K



Detect

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[FDSD001R](#) [FDSD002R](#)