

FP Series Sealed Ultra Miniature Pushbutton Switches




A
Pushbutton

Features/Benefits

- Ultra-miniature pushbutton
- Multiple poles and throws
- Long life 100,000 cycles
- Vertical and right angle mount
- Sealed against soldering and cleaning processes
- Optional caps
- RoHS compliant

Typical Applications

- Networking equipment
- High-end consumer
- Professional instrumentation
- Computer, Server, Modem & Data storage



Specifications

CONTACT RATING: Max. 0.4 VA (28 V DC or V AC)
 ELECTRICAL LIFE: 50,000 cycles (FP11 & FP21)
 10,000 cycles (FP12 & FP22)
 CONTACT RESISTANCE: (10mA @ 2 V DC) 80 mΩ max. initial
 INSULATION RESISTANCE: 500MΩ min. @ 500 V DC - 1 minute
 OPERATING TEMPERATURE: -20°C to 80°C
 SOLDERABILITY: Per MIL-STD-202F method 208D, or
 EIA RS-186E method 9
 PACKAGING:
 Tray pack - 25 pcs per tray (A1 type terminal)
 - 100 pcs per tray (C1 type terminal)
 Caps (optional) - Bulk bag; 100 caps per bag.

Materials

MOVABLE CONTACTS:
 Base metal: Phosphor bronze
 Plating: Gold over nickel plate
 FIXED CONTACTS:
 Base metal: Brass
 Plating: Gold over nickel plate
 COVER: PA66 - Black
 ACTUATOR: PPS - Black
 BASE: PPS - Black
 SUPPORT BRACKET: Steel with tin plate
 (A1 type terminal only)

NOTE: Specifications and materials listed above are for switches with standard options.
 For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages A-106 thru A-107. For additional options not shown in catalog, consult Customer Service Center.





	F	P		S	P		B	1	T	P	
Designation											
FP11	SPST N.O.										
FP12	SPDT N.O.										
FP21	DPST N.O.										
FP22	DPDT N.O.										
Actuator Length											
SP	Standard plunger 3.3mm										
Terminal Style											
C1	Vertical										
A1	Right Angle										
Contact Plating											
B1	Gold over nickel plate										
Packaging											
TP	Tray packaging										
Cap											
00	No cap										
01	White cap - bulk bagged										
02	Black cap - bulk bagged										
03	Red cap - bulk bagged										



SWITCH CIRCUIT

TERMINAL STYLE

A1 RIGHT ANGLE



www.ckswitches.com

FP Series Sealed Ultra Miniature Pushbutton Switches




A

Pushbutton


ACTUATOR LENGTH

SP STANDARD PLUNGER 3.3MM



CAPS

OPTION CODE	DESCRIPTION
00	NO CAP
01	WHITE CAP, BULK BAGGED
02	BLACK CAP, BULK BAGGED
03	RED CAP, BULK BAGGED



To purchase Caps separately without switch, please use these part numbers


PART #	COLOR
798D01000	WHITE
798D02000	BLACK
798D03000	RED

MOUNTING HOLE


C1 VERTICAL




FP11




FP12







FP21



FP22



A1 RIGHT ANGLE



Dimensions are shown: mm
Specifications and dimensions subject to change

C&K

13 Mar 20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[FP12SPA1B1TP00](#) [FP12SPC1B1TP00](#) [FP21SPC1B1TP00](#) [FP22SPC1B1TP00](#) [FP21SPA1B1TP00](#)
[FP22SPA1B1TP00](#)