

Mega Sample Kit

MS12 15102

Max Dia = 13.5mm $\pm$ 15%

R@25°C = 150 Ω $\pm$ 25 %

SSI = 2.0 A

Energy = 100 J

MS15 30004

Max Dia = 17.0mm $\pm$ 10%

R@25°C = 30.0 Ω $\pm$ 25%

SSI = 4.20 A

Energy = 120 J

MS22 10008

Max Dia = 22.0mm $\pm$ 10%

R@25°C = 10 Ω $\pm$ 25%

SSI = 8.00 A

Energy = 200 J

MS22 50004

Max Dia = 22.0mm $\pm$ 10%

R@25°C = 50.0 Ω $\pm$ 25%

SSI = 4.00 A

Energy = 240 J

MS35 10018

Max Dia = 35.0mm $\pm$ 10%

R@25°C = 10.0 Ω $\pm$ 25%

SSI = 18.00 A

Energy = 500 J

MS32 10015

Max Dia = 31.0mm $\pm$ 10%

R@25°C = 10.0 Ω $\pm$ 25%

SSI = 15.00 A

Energy = 250 J

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[MS sample kit](#)