




| | | |
|-----|----------|------|
| REV | DATE | ECD# |
| A | 03/31/95 | 1342 |
| | | |

DRAWING NOT TO SCALE
ALL DIMENSIONS IN INCHES



SPECIFICATIONS:
 RESISTANCE AT 25 DEG C = 4 OHMS +/- 15%
 MAX CONTINUOUS CURRENT (I_{max}) = 8 AMPS
 RESISTANCE AT I_{max} = 0.07 OHMS NOMINAL
 MAX VOLTAGE RATING = 265 VAC (RMS)
 MAX SURGE RATING = 27 JOULES
 ENCAPSULATION = SILICONE RESIN
 MARKING = OPTIONAL
 LEADS = RODAN P/N STL-209-35

| | | |
|--------------------|----------------|--|
| DRAWN BY D. NGUYEN | |  Circuit Protection Thermistors |
| DATE 09/25/90 | ORIG. F. TISED | |
| REV A | APP | SURGE-GARD INRUSH CURRENT LIMITER |
| SHEET 1 OF 1 | | SG308 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SG308](#)