


Part Number: SM06 103370



### Electrical Specifications:

|                                             |                         |
|---------------------------------------------|-------------------------|
| Resistance @ 25°C                           | 10.0K $\Omega \pm 10\%$ |
| Beta                                        | 3700 $\pm 2\%$          |
| Temperature Coefficient ( $\alpha$ )        | -4.5% / °C              |
| Dissipation Constant                        | 1.50 mW/°C              |
| Thermal Time Constant                       | 5.0 Seconds             |
| Maximum Continuous Power (P <sub>25</sub> ) | 200.0 mW                |
| Operating Temperature                       | -40 °C $\approx$ +125°C |
| Termination                                 | Nickel Barrier          |
| Material Type                               | "N"                     |

### Mechanical Specifications:

|                |                               |
|----------------|-------------------------------|
| L              | 1.6 $\pm$ 0.15 mm             |
| W              | 0.80 $\pm$ 0.15 mm            |
| T              | 0.5 $\pm$ 0.10 mm             |
| L <sub>1</sub> | 1.20 $\pm$ 0.20 mm            |
| Tape & Reel    | Per Mil Std 201<br>Method 208 |
| Qty/Reel       | 5000 pcs                      |

Revision Date: March 19, 2003

**Ametherm, Inc.** 3111 N. Deer Run Road #4 Carson City, NV 89701

Telephone: (800) 808-2434 (775) 884-2434 Fax: (775) 884-0670

[www.ametherm.com](http://www.ametherm.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SM06 103370](#)