

# Toggle Switches



SERIES	FEATURE	ACTUATION	MAX RATING (Resistive @ 28VDC)	SEAL RATING	MOUNTING	CIRCUITRY
T1	2 or 3 Position, 1 to 8 Poles, Lever Lock Option	Momentary, Maintained	8A	MIL-PRF-83731	15/32" or 7/16" Threaded	Multi-Pole B2, B3 Basics
T3	Snap Action, Lever Lock Option	Momentary, Maintained	5A	MIL-PRF-83731 - 15/32" Threaded Only	15/32" or 1/4" Threaded	SPST, DPST
T7	Lower Cost, Sealed	Momentary, Maintained	16A	IP68S & IP69K	15/32" Threaded	SPST, SPDT DPST, DPDT
T71	Thinner T7 Sealed	Momentary, Maintained	16A	IP68S & IP69K	15/32" Threaded	SPST, SPDT
T9	High Performance Lever Lock Option	Momentary, Maintained	20A	IP68S or MIL-DTL-3950	15/32" Threaded	SPST, SPDT DPST, DPDT
TE	Snap Action, Non-Teasible	Momentary, Maintained	5A	MIL-DTL-8834	15/32" or 1/4" Threaded	SPST, DPST

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[OTTO:](#)

[T1-0234](#) [T1-0243](#) [T1-0011](#) [T1-0013](#) [T1-0209-2](#) [T1-0232](#) [T1-0012](#) [T1-0105](#) [T1-0381](#) [T1-0124](#) [T1-0218](#) [T1-0334](#)  
[T1-0119D](#) [T1-0162](#) [T1-0216L10](#) [T1-0284](#) [T1-0351](#) [T1-0230](#) [T1-0030](#) [T1-0088](#) [T1-0015](#) [T1-0091-2](#) [T1-0209-1](#)  
[T1-0209-3](#) [T1-0264](#) [T1-0144](#) [T1-0246K](#) [T1-0434](#) [T1-0119F](#) [T1-0023-1](#) [T1-0160](#) [T1-0195N](#) [T1-0241](#) [T1-0170](#) [T1-](#)  
[0244](#) [T1-0280](#) [T1-0332](#) [T1-0355](#) [T1-0250](#) [T1-0149](#) [T1-0191K](#) [T1-0292](#) [T1-0028](#) [T1-0126](#) [T1-0195L](#) [T1-0201D](#)  
[T1-0239](#) [T1-0333](#) [T1-0055](#) [T1-0156](#) [T1-0049](#) [T1-0191P](#) [T1-0246E](#) [T1-0038](#) [T1-0194L](#) [T1-0291](#) [T1-0213](#) [T1-0446](#)  
[T1-0098](#) [T1-0209-4](#) [T1-0265](#) [T1-0344D](#)