

Johanson Company: Johanson Technology inc. Product Release Date: 29 August, 2018

Deprecated P/N: 2000BP44A1000E

Thickness (Max): 0.059

Datasheet Date: 08-09-2024

End Band (Min):

Description: Band Pass Filters, 1812,
1500-2500MHz, 0.5W, 2.5dB, Ni/Sn (RoHS), 2 GHz
Band Pass Filter, 7" Reel Embossed Tape

End Band (Max):

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important
to obtain a quotation with lead time for
production planning purposes. 20

Life Cycle Stage: Active - Production

Schedule B: 8534

Length (Min): 0.169

ECCN: EAR99

Length (Max): 0.185

RoHS Compliance: Yes, RoHS 10/10

Width (Min): 0.118

REACH: 1

Width (Max): 0.134

Country of Origin: TW

Packaging: 7" Reel Embossed Tape

Product Family: Integrated Passive Components

Packaging Qty: 1000

Product Subfamily: Band Pass Filters

Operating Temp Range: -40°C to +85°C

Marking: Special

Storage Temp Range (Packaged): -40°C to +85°C

Storage Temp Range (Non Operating): +5°C to
+35°C with RH 45% to 75%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[2000BP44A1000E](#)