

Johanson Company: Johanson Technology inc. Product Release Date: 26 October, 2017

Deprecated P/N: 5235BP45A0180E

Thickness (Max): 0.124

Datasheet Date: 08-09-2024

Thickness (Min): 0.104

Description: Band Pass Filters, 3415,
5150-5330MHz, 1W, 2.4/2.5dB, Ag/Pt (RoHS),
5.24GHz High Rejection UNII-low Band Pass Filter,
7" Reel Embossed Tape

End Band (Min):

End Band (Max):

Life Cycle Stage: Active - Production

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important
to obtain a quotation with lead time for
production planning purposes. 20

Schedule B: 8534

Length (Min): 0.327

ECCN: EAR99

Length (Max): 0.347

RoHS Compliance: Yes, RoHS 10/10

Width (Min): 0.142

REACH: 1

Width (Max): 0.162

Country of Origin: TW

Packaging: 7" Reel Embossed Tape

Product Family: Integrated Passive Components

Packaging Qty: 1000

Product Subfamily: Band Pass Filters

Operating Temp Range: -40°C to +100°C

Marking: Special

Storage Temp Range (Packaged): -40°C to
+105°CStorage Temp Range (Non Operating): +5°C to
+35°C with RH 45% to 75%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[5235BP45A0180E](#)