

Johanson Product Information for 5500BP15A0700001E

Johanson Company: Johanson Technology inc. Product Release Date: 21 January, 2019

Deprecated P/N: 5500BP15A0700E

Thickness (Max): 0.031

Datasheet Date: 08-10-2024

End Band (Min):

Description: Band Pass Filters, 805,
5150-5850MHz, 3W, 1.25dB, Ni/Sn (RoHS),
5.5GHz Band Pass Filter, EIA 0805, 7" Reel
Embossed Tape

End Band (Max):

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important
to obtain a quotation with lead time for
production planning purposes. 20

Life Cycle Stage: Active - Production

Length (Min): 0.075

Schedule B: 8534

Length (Max): 0.083

ECCN: EAR99

Width (Min): 0.045

RoHS Compliance: Yes, RoHS 10/10

Width (Max): 0.053

REACH: 1

Packaging: 7" Reel Embossed Tape

Country of Origin: TW

Packaging Qty: 4000

Product Family: Integrated Passive Components

Operating Temp Range: -40°C to +95°C

Product Subfamily: Band Pass Filters

Storage Temp Range (Packaged): -40°C to +95°C

Marking: Special

Storage Temp Range (Non Operating): +5°C to
+35°C with RH 55% to 75%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[5500BP15A0700E](#)