

Johanson Product Information for 5500BP41A0665001E

**Johanson Company: Johanson Technology inc.** Product Release Date: 21 January, 2019

Deprecated P/N: 5500BP41A0665E

Datasheet Date: 08-09-2024

Description: Band Pass Filters, 1210,  
5170-5835MHz, 3W, 2.5dB, Ni/Sn (RoHS), 5.5GHz  
Band Pass Filter, EIA 1210, 7" Reel Embossed  
Tape

Life Cycle Stage: Active - Production

Schedule B: 8534

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Integrated Passive Components

Product Subfamily: Band Pass Filters

Marking: Special

Web Page Link:

<https://www.johansontechnology.com/band-pass-filters>

Thickness (Max): 0.071

End Band (Min):

End Band (Max):

Lead Time Typical (Weeks)\*:

\*This can vary significantly so it is important  
to obtain a quotation with lead time for  
production planning purposes. 20

Length (Min): 0.118

Length (Max): 0.134

Width (Min): 0.090

Width (Max): 0.106

Packaging: 7" Reel Embossed Tape

Packaging Qty: 2000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): -40°C to +95°C

Storage Temp Range (Non Operating): +5°C to  
+35°C with RH 55% to 75%

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[5500BP41A0665E](#)