

**Johanson Company: Johanson Technology inc.** Product Release Date: 26 October, 2017

Deprecated P/N: 5697BP45A0360E

Thickness (Max): 0.124

Datasheet Date: 08-09-2024

Thickness (Min): 0.104

Description: Band Pass Filters, 3413,  
5490-5850MHz, 1W, 1.5/2.5dB, Ag/Pt (RoHS),  
5.67GHz High Rejection UNII-High, Band Pass  
Filter, 7" Reel Embossed Tape

End Band (Min):

End Band (Max):

Life Cycle Stage: Active - Production

Lead Time Typical (Weeks)\*:

\*This can vary significantly so it is important  
to obtain a quotation with lead time for  
production planning purposes. 20

Schedule B: 8534

Length (Min): 0.327

ECCN: EAR99

Length (Max): 0.347

RoHS Compliance: Yes, RoHS 10/10

Width (Min): 0.118

REACH: 1

Width (Max): 0.138

Country of Origin: TW

Packaging: 7" Reel Embossed Tape

Product Family: Integrated Passive Components

Packaging Qty: 1000

Product Subfamily: Band Pass Filters

Operating Temp Range: -40°C to +100°C

Marking: Special

Storage Temp Range (Packaged): -40°C to  
+105°CStorage Temp Range (Non Operating): +5°C to  
+35°C with RH 45% to 75%

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[5697BP45A0360E](#) [5697BP45A0360001E](#)