

High Frequency Ceramic Solutions

2450 MHz Directional Coupler Ceramic SMD

P/N 2450CP14B100

Detail Specification: 02/01/12

Page 1 of 2

General Specifications

Part Number	2450CP14B100
Frequency (MHz)	2400 - 2500
Insertion Loss	0.34 dB max.
Return Loss	15.6 dB min.
Coupling	17.65 ± 1.0 dB
Isolation	25.0 dB min.

Impedance	50 Ω
Input Power	3 Watt max.
Operating Temperature	-40 to +85°C
Storage Conditions	+5 to +35°C, 45-75%RH
Reel Quantity	4,000



P/N Suffix	Packaging Style	Bulk	Suffix = S	Eg. 2450CP14B100S
		T & R	Suffix = T	Eg. 2450CP14B100T
	Termination Style	100% Tin	Suffix = None	Eg. 2450CP14B100(T or S)
		Tin / Lead	Suffix = /Pb	Eg. 2450CP14B100(T or S)/Pb

Terminal Configuration

No.	Function
1	IN
2	GND
3	Coupled Out
4	Termination
5	GND
6	Main Out

Mechanical Dimensions

	In	mm
L	0.063 ± 0.004	1.60 ± 0.10
W	0.031 ± 0.004	0.80 ± 0.10
T	0.024 ± 0.004	0.60 ± 0.10
a	0.008 ± 0.004	0.20 ± 0.10
b	0.008 +.004/-0.006	0.20 +0.1/-0.15
c	0.006 ± 0.004	0.15 ± 0.10
g	0.012 ± 0.004	0.30 ± 0.10
p	0.020 ± 0.002	0.50 ± 0.05




Mounting Considerations

Mount these devices with brown mark facing up.

* Line width should be designed to provide 50 ohm impedance, depending on PCB material and thickness

Units: mm



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2012 Johanson Technology, Inc. All Rights Reserved

High Frequency Ceramic Solutions


2450 MHz Directional Coupler Ceramic SMD

P/N 2450CP14B100

Detail Specification: 02/01/12

Page 2 of 2

Typical Electrical Performance (T=25°C)



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2012 Johanson Technology, Inc. All Rights Reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[2450CP14B100T](#) [2450CP14B0100001T](#)