


SURFACE MOUNT MLCCs 10 - 200 VDC

CASE SIZE			Voltage	AVAILABLE CAPACITANCE CODE																					
JDI	Inches	(mm)		0R5	XRX	100	120	150	180	220	270	330	390	470	560	680	820	101	121	151	181	221	271	331	391
R05	0201	(0603)																							
			25V																						
			16V																						
			10V																						
R07	0402	(1005)	50V																						
			25V																						
			16V																						
			10V																						
R14	0603	(1608)	200V																						
			100V																						
			50V																						
			25V																						
			16V																						
R15	0805	(2012)	200V																						
			100V																						
			50V																						
			25V																						
			16V																						
R18	1206	(3216)	200V																						
			100V																						
			50V																						
			25V																						
			16V																						
S41	1210	(3224)	200V																						
			100V																						
			50V																						
			25V																						
			16V																						
S43	1812	(4532)	200V																						
			100V																						
			50V																						
			25V																						
			16V																						



How To ORDER - SURFACE MOUNT MLCC

Part number written: 100R07W104KV4E

100	R 07	W	104	K	V	4	E
VOLTAGE	SERIES/SIZE	DIELECTRIC	CAPACITANCE	TOLERANCE	TERMINATION	MARKING	PACKING
100 = 10 V DC 160 = 16 V DC 250 = 25 V DC 500 = 50 V DC 101 = 100 V DC 201 = 200 V DC	R05 = 0201 R07 = 0402 R14 = 0603 R15 = 0805 R18 = 1206 S41 = 1210 S43 = 1812	N = NP0 W = X7R X = X5R	1st two digits are significant; third digit denotes number of zeros, R = decimal. 5R6 = 5.6 pF 100 = 10 pF 102 = 1,000 pF 474 = 0.47 μF	* B = ± 0.10 pF * C = ± 0.25 pF * D = ± 0.50 pF F = ± 1 % G = ± 2 % J = ± 5 % K = ± 10 % M = ± 20 % *Values < 10 pF only	V = Nickel Barrier with 100% Tin Plating (Matte) T = SnPb	3 = Special 4 = Unmarked 6 = EIA Code* *Not available on sizes ≤ 0402	E = Embossed 7" T = Punched 7" U = Embossed 13" R = Punched 13" No code = bulk Tape specifications on page 48. Not all tape styles are available on all parts.

See Tanceram High
Capacitance Series
for values $\geq 1.0\mu\text{F}$

Please refer to page 78 of the catalog or www.johansondielectrics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Johanson:

[101R14N101GV4T](#) [101R14W103KV4T](#) [101R14N3R9BV4T](#) [101R14W102KV4T](#) [101R14W681KV4T](#)
[101R14N470JV4T](#) [101R14N220GV4T](#) [101R14N820JV4T](#) [101R18W104KV4E](#) [101R14W821KV4T](#)
[101R15N102GV4T](#) [101R14N101JV4T](#) [101R14W471KV4T](#) [101R14N470GV4T](#) [101R14N0R5BV4T](#)
[101R14N390GV4T](#) [101R14N270JV4T](#) [101R14N6R8CV4T](#) [101R14N1R0CV4T](#) [101R14N680JV4T](#) [101R15N331JV4T](#)
[101R15N101JV4T](#) [101R18W103MV4T](#) [101R15W222MV4T](#) [101R14W102MV4T](#) [101R15W153MV4T](#)
[101R18W103KV4T](#) [101R14W332KV4T](#) [101R14W561KV4T](#) [101R14W392MV4T](#) [101R15W222KV4T](#)
[101R14W103MV4T](#) [101R15W472KV4T](#) [500S43W564KV4E](#) [101S41W224KV4E](#) [101R14W331KV4T](#)
[101R18W153KV4T](#) [101R18W223KV4T](#) [101R15W223KV4T](#) [101R15W392KV4T](#) [101R14W222KV4T](#)
[101R15W272MV4T](#) [101R15W822KV4T](#) [101R15W103KV4T](#) [101R18W473KV4T](#) [101R14N120KV4T](#)
[101R14W152JV4T](#) [101R15W562JV4T](#) [101R15N270FV4T](#) [101R14W471JV4T](#) [101R14N100FV4T](#) [101R15W332JV4T](#)
[101R15N100JV4T](#) [101R14N100KV4T](#) [101R18N220JV4T](#) [101R14N1R0BV4T](#) [101R18N471JV4T](#) [101R15N221JV4T](#)
[101R18N121KV4T](#) [101R15N470KV4T](#) [101R15N330FV4T](#) [101R18N102JV4T](#) [101R15N471GV4T](#)
[101R14N270KV4T](#) [101R15N390JV4T](#) [101R18N331JV4T](#) [101R15N150JV4T](#) [101R14N270GV4T](#) [101R14N220JV4T](#)
[101R18N181KV4T](#) [101R18W103JV4T](#) [101R15W103JV4T](#) [101R14N100JV4T](#) [101R15N560JV4T](#) [101R18N121JV4T](#)
[101R15N150KV4T](#) [101R14N121KV4T](#) [101R14N470FV4T](#) [101R14N1R5BV4T](#) [101R18N681KV4T](#) [101R18N151KV4T](#)
[101R15N270GV4T](#) [101R14N470KV4T](#) [101R15N820FV4T](#) [101R15N680JV4T](#) [101R14N820FV4T](#)
[101R14W102JV4T](#) [101R18N101JV4T](#) [101R15N101FV4T](#) [101R14N101KV4T](#) [101R18N221KV4T](#) [101R14N151JV4T](#)
[101R14N120JV4T](#) [101R14W681JV4T](#) [101R14N221GV4T](#) [101R15N1R8CV4T](#) [101R15N330JV4T](#)
[101R15N391JV4T](#) [101R15N821JV4T](#) [101R15N471JV4T](#)