

PLUG: MM-212-025-175-320S
RECEPTACLE: MM-222-025-261-41WQ
PLUG: MN-211-025-175-320S
RECEPTACLE: MN-221-025-261-41WQ
 XX-XXX-XXX-XXX-XXXX-XXX

PLUG
RECEPTACLE

SERIES	
MM .050" Rugged Metal PC Board Mount, SMT Connector	MM .050" Rugged Metal I/O Connector
MN .050" Rugged Plastic PC Board Mount, SMT Connector (MM & MN mate with MK, ML, MM, MN receptacles)	MN .050" Rugged Plastic I/O Connector (MM & MN mate with MK, ML, MM, MN plugs)

BODY	
2 2-Row (Sizes 9 thru 51***)	2 2-Row (Sizes 9 thru 51***)
BODY STYLE:	BODY STYLE:
1 Plug, straight, with ears	2 Receptacle, straight, with ears
BODY MATERIAL:	BODY MATERIAL:
1 Polyphenylene Sulfide (MN only)	1 Polyphenylene Sulfide (MN only)
2 Polyphenylene Sulfide with electroless nickel shell	2 Polyphenylene Sulfide with electroless nickel shell
3 Polyphenylene Sulfide with electrodeposited cadmium shell	3 Polyphenylene Sulfide with electrodeposited cadmium shell
4 Polyphenylene Sulfide with hard anodized black shell	4 Polyphenylene Sulfide with hard anodized black shell
5 Polyphenylene Sulfide with stainless steel shell	5 Polyphenylene Sulfide with stainless steel shell

SIZE	
XXX 009, 015, 021, 025, 031, 037, 051***	XXX 009, 015, 021, 025, 031, 037, 051***

CONTACTS	
TYPE CONTACTS/TERMINATIONS:	TYPE CONTACTS/TERMINATIONS:
17 Pin, Surface Mount	21 Socket, straight, solder cup
	24 Socket, straight, .500" pigtails (.018 dia)
	25 Socket, straight, 1.000" pigtails (.018 dia)
	26 Socket, straight, crimped wire
PLATING OPTIONS:	PLATING OPTIONS:
5 50 µ" Au contacts; 100 µ" Sn alloy terminations	1 50 µ" Au contacts (crimp wire)
	3 50 µ" Au contacts: 10 µ" Au terminations (solder cup, pigtail)
	5 50 µ" Au contacts; 100 µ" Sn alloy terminations (pigtail)

HARDWARE	
STYLE OF HARDWARE:	STYLE OF HARDWARE:
00 None	00 None
32 Two fixed jacknut assemblies with mounting bracket	22 Two fixed jacknut assemblies
46 Two turning jackscrews, allen head, captivated** with mounting bracket	41 Two turning jackscrews, allen head, retaining ring
	42 Two long turning jackscrews, allen head, retaining ring
	43 Two turning jackscrews, slot head, retaining ring
	44 Two long turning jackscrews, slot head, retaining ring
	45 Two turning jackscrews, allen head, captivated**
POLARIZATION / WIRING:	POLARIZATION / WIRING
0R Reverse Body Polarization	00 None
0S Standard Body Polarization	XX For wiring codes, see page MA-3 & MA-4

OPTIONS	
	900 Interfacial sealing gasket

** = Captive hardware is factory installed and non-removable.
 *** = 51 position connectors are available in metal only (non Mil-Spec interface).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[MM-222-037-261-22WP](#)