

PLUG: MM-312-051-153-4400
RECEPTACLE: MK-322-051-235-2200
PLUG: MN-311-051-153-4400
RECEPTACLE: ML-321-051-235-2200
 XX-XXX-XXX-XXX-XXXX-XXX

PLUG
RECEPTACLE

SERIES	
MM .050" Rugged Metal I/O Connector MN .050" Rugged Plastic I/O Connector (MM & MN mate with MK, ML, MM, MN receptacles)	MK .050" Rugged Metal PC Board Mount Connector ML .050" Rugged Plastic PC Board Mount Connector (MK & ML mate with MK, ML, MM, MN plugs)
BODY	
2 2-Row (Sizes 9 thru 37) 3 3-Row (Size 51) 4 4-Row (Size 100) BODY STYLE: 1 Plug, straight, with ears BODY MATERIAL: 1 Polyphenylene Sulfide (MN only) 2 Polyphenylene Sulfide with electroless nickel shell 3 Polyphenylene Sulfide with electrodeposited cadmium shell ☒ 4 Polyphenylene Sulfide with hard anodized black shell 5 Polyphenylene Sulfide with stainless steel shell A Pure Electro-Deposited Aluminum K Zinc Nickel Plating T Nickel Polymer Plating	2 2-Row (Sizes 9 thru 37) 3 3-Row (Size 51) 4 4-Row (Size 100) BODY STYLE: 2 Receptacle, straight, narrow footprint, w/ mtg holes BODY MATERIAL: 1 Polyphenylene Sulfide (ML only) 2 Polyphenylene Sulfide with electroless nickel shell 3 Polyphenylene Sulfide with electrodeposited cadmium shell ☒ 4 Polyphenylene Sulfide with hard anodized black shell 5 Polyphenylene Sulfide with stainless steel shell A Pure Electro-Deposited Aluminum K Zinc Nickel Plating T Nickel Polymer Plating
SIZE	
XXX 009, 015, 021, 025, 031, 037, 051, 100	XXX 009, 015, 021, 025, 031, 037, 051, 100
CONTACTS	
TYPE CONTACTS/TERMINATIONS: 11 Pin, straight, solder cup 14 Pin, straight, .500" pigtails (.018 dia) 15 Pin, straight, 1.000" pigtails (.018 dia) 16 Pin, straight, crimped wire PLATING OPTIONS: 1 50 µ" Au contacts (crimp wire) 3 50 µ" Au contacts: 10 µ" Au terminations (solder cup, pigtail) 5 50 µ" Au contacts; Sn/Pb alloy terminations (pigtail) ☒ 7 50 µ" Au contacts; SAC305 terminations (pigtail)	TYPE CONTACTS/TERMINATIONS: 22 Socket, straight, PCB leads, .109" 23 Socket, straight, PCB leads, .140" 24 Socket, straight, PCB leads, .172" PLATING OPTIONS: 3 50 µ" Au contacts: 10 µ" Au terminations 5 50 µ" Au contacts; Sn/Pb alloy terminations ☒ 7 50 µ" Au contacts; SAC305 terminations
HARDWARE	
STYLE OF HARDWARE: 00 None 22 Two fixed jacknut assemblies (62*) 41 Two turning jackscrews, allen head, retaining ring (81*) Two long turning jackscrews, allen head, retaining ring (82*) 43 Two turning jackscrews, slot head, retaining ring (83*) 44 Two long turning jackscrews, slot head, retaining ring (84*) 45 Two turning jackscrews, allen head, captivated** (85*) 99 Keying hardware, see options below (Body material 2, 3 and 4 only)	STYLE OF HARDWARE: 00 None 22 Two fixed jacknut assemblies (62*) 99 Keying hardware, see options below (Body material 2, 3 and 4 only)
POLARIZATION / WIRING: 00 None XX For wiring codes, see page MA-3 & MA-4	POLARIZATION / WIRING 00 None
OPTIONS	
K5XX Two turning jackscrews. See page MA-6 for keying options (KJ*)	KPXX Two fixed jacknuts and interfacial sealing gasket. See page MA-6 for keying options (KN*) 900 Interfacial sealing gasket 0B7 Threaded inserts and interfacial sealing gasket

* = Use numbers or letters in parenthesis when ordering size 100.

** = Captive hardware is factory installed and non-removable.

☒ = Option not RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[M83513/25-C01NN](#) [M83513/25-C02NN](#) [M83513/25-D01NN](#) [M83513/25-D02CN](#) [M83513/25-F03CN](#) [M83513/27-H01NN](#) [M83513/25-C03NN](#) [M83513/25-D03CP](#) [M83513/25-F02CP](#) [M83513/25-F02NP](#) [M83513/25-A03CP](#) [M83513/25-E03CN](#) [M83513/26-G02CN](#) [M83513/26-G03NN](#) [M83513/25-D03CN](#) [M83513/25-F03NN](#) [M83513/26-G01NN](#) [M83513/27-H01CN](#) [M83513/25-B01CT](#) [M83513/25-C03CP](#) [M83513/25-E03CP](#) [M83513/25-A03NN](#) [M83513/25-C02NP](#) [M83513/25-E02NN](#) [M83513/26-G02NN](#) [M83513/26-G03CN](#) [M83513/25-A01CP](#) [M83513/25-B01NN](#) [M83513/25-B02CN](#) [M83513/25-E01NN](#) [M83513/25-F01NN](#) [M83513/25-A01CN](#) [M83513/25-B03CN](#) [M83513/25-D03NN](#) [M83513/25-E01CN](#) [M83513/25-F02CN](#) [M83513/25-F02NN](#) [M83513/27-H03NP](#) [M83513/25-B01CN](#) [M83513/25-D01CN](#) [M83513/25-B03NP](#) [M83513/25-D01NP](#) [M83513/27-H02CN](#) [M83513/25-A02CP](#) [M83513/25-B01NP](#) [M83513/25-D02NP](#) [M83513/25-E01NP](#) [M83513/27-H01CP](#) [M83513/25-B02CP](#) [M83513/25-E02CP](#) [M83513/25-E03NN](#) [M83513/26-G01CP](#) [M83513/25-A03CN](#) [M83513/27-H03CN](#) [M83513/25-B02NN](#) [M83513/25-B03NN](#) [M83513/27-H03NN](#) [M83513/25-D03NP](#) [M83513/25-E02NP](#) [M83513/25-A01NP](#) [M83513/25-C02CN](#) [M83513/25-F01CN](#) [M83513/25-F03CP](#) [M83513/25-A02CN](#) [M83513/25-E02CN](#) [M83513/25-E03NP](#) [M83513/25-C01CP](#)