

PLUG		RECEPTACLE		RECEPTACLE: MD 021 RS M2 45 XX XXX XX XX XX					
SERIES									
MD .050" Rugged Metal Dust Cover		MD .050" Rugged Metal Dust Cover							
SIZE									
XXX 009, 015, 021, 025, 031, 037, 051, 069, 100		XXX 009, 015, 021, 025, 031, 037, 051, 069, 100							
STYLE									
RP Plug, rugged metal		RS Receptacle, rugged metal							
PLATING									
M2 Electroless nickel		M2 Electroless nickel							
M3 Electrodeposited cadmium ☒		M3 Electrodeposited cadmium ☒							
M4 Hard anodized black		M4 Hard anodized black							
HARDWARE									
STYLE OF HARDWARE:		STYLE OF HARDWARE:							
22 Two integrated jacknuts (62")		22 Two integrated jacknuts (62")							
45 Two turning jackscrews, allen head, captivated** (85")		45 Two turning jackscrews, allen head, captivated** (85")							

* = Use number in parenthesis when ordering size 100.

** = Captive hardware is factory installed and non-removable.

Not for use with rear panel mount connectors

Not for use on receptacles with grounding fingers

☒ = Option not RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[MD100RS](#) [MD100RP](#) [MD009RPM245](#) [MD009RSM245](#) [MD015RSM245](#) [MD037RSM245](#)