

**PLUG COVER:** ND-1P2-009-JC  
**RECEPTACLE COVER:** ND-1R2-009-TH  
 XX-XXX-XXX-XX

PLUG COVER		RECEPTACLE COVER	
<b>SERIES</b>			
ND .025" Metal Dust Cover		ND .025" Metal Dust Cover	
<b>BODY</b>			
1	1-Row	1	1-Row
<b>BODY STYLE:</b> P Plug cover		<b>BODY STYLE:</b> R Receptacle cover	
<b>BODY PLATING:</b> 2 Electroless nickel 3 Electrodeposited cadmium <input type="checkbox"/>		<b>BODY PLATING:</b> 2 Electroless nickel 3 Electrodeposited cadmium <input type="checkbox"/>	
<b>SIZE</b>			
XXX 009, 015, 021, 025, 031, 037 or 051		XXX 009, 015, 021, 025, 031, 037 or 051	
<b>HARDWARE</b>			
<b>STYLE OF HARDWARE:</b> JC Turning jackscrews, captivated #0-80 UNF* TH Threaded hole, #0-80 UNF		<b>STYLE OF HARDWARE:</b> JC Turning jackscrews, captivated #0-80 UNF* TH Threaded hole, #0-80 UNF	

\* = Recommended torque value 1.0 inch-lbs. max.  
 Ball end hex wrench not recommended  
 Hex wrench key/bit conforming to the requirements of ASME / ANSI-B-18.3 is recommended.  
 .050" hex L-key long arm wrench - order AirBorn p/n CDG14148.

☐ = Option not RoHS compliant

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[ND-1P2-015-JC](#) [ND-1P2-025-JC](#)