

PLUG: RM352-152-321-5500
 RECEPTACLE: RM322-152-211-5500
 XXXXX-XXX-XXX-XXXXXX

PLUG

RECEPTACLE

SERIES

RM .075" Screw Machine PC Connector | RM .075" Screw Machine PC Connector

BODY

3 3-Row	3 3-Row
BODY STYLE:	BODY STYLE:
5 Plug, right angle, with mounting ears	2 Receptacle, straight, with mounting ears
7 Plug, right angle, without mounting ears	4 Receptacle, straight, without mounting ears
BODY MATERIAL:	BODY MATERIAL:
2 Polyphenylene sulfide (PPS)	2 Polyphenylene sulfide (PPS)

SIZE

011, 023, 035, 047, 059, 071, 080, 092, 104, 122, 140, 152, 182, 206 | 011, 023, 035, 047, 059, 071, 080, 092, 104, 122, 140, 152, 182, 206

CONTACTS

TYPE CONTACTS/TERMINATIONS:	TYPE CONTACTS/TERMINATIONS:
31 Pin, right angle, dip solder, .109" x .020" dia	20 Socket, straight, dip solder, .109" x .020" dia
32 Pin, right angle, dip solder, .140" x .020" dia	21 Socket, straight, dip solder, .140" x .020" dia
33 Pin, right angle, dip solder, .172" x .020" dia	22 Socket, straight, dip solder, .172" x .020" dia
34 Pin, right angle, dip solder, .109" x .016" dia	23 Socket, straight, dip solder, .250" x .020" dia
35 Pin, right angle, dip solder, .140" x .016" dia	24 Socket, straight, solder cup
36 Pin, right angle, dip solder, .172" x .016" dia	25 Socket, straight, flex circuit, .093" x .017" dia
37 Pin, right angle, dip solder, .250" x .020" dia	26 Socket, straight, wire wrap®, .500" x .018 sq
	27 Socket, straight, wire wrap®, .375" x .018 sq
	28 Socket, straight, wire wrap®, .625" x .018 sq
	29 Socket, connector saver, .150" x .025" dia
	50 Socket, straight, dip solder, .140" x .016" dia
	51 Socket, straight, dip solder, .172" x .016" dia
	53 Socket, straight, stacking, .212" x .025" dia
	54 Socket, straight, stacking, .244" x .025" dia
	55 Socket, straight, stacking, .275" x .025" dia
	64 Socket, straight, press-fit, .203" (Board .093"-.125" thk)
	65 Socket, straight, press-fit, .323" (Board .156"-.200" thk)
	66 Socket, straight, press-fit, .403" (Board .250"+ thk)

PLATING OPTIONS:	PLATING OPTIONS:
1 Gold plated termination	1 Gold plated termination
2 Pre-tinned termination, SnPb alloy ☒	2 Pre-tinned termination, SnPb alloy (dip solder options only) ☒
3 Pre-tinned termination, SAC305 alloy	3 Pre-tinned termination, SAC305 alloy (dip solder options only)

HARDWARE

STYLE OF HARDWARE: (See R-41 & R-42 for all options)	STYLE OF HARDWARE: (See R-41 & R-42 for all options)
0256 None	0256 None
55 Guide set	55 Guide set
57 Two guide pins	57 Two guide pins
58 Two guide sockets	58 Two guide sockets
29 Fixed jackset	29 Fixed jackset
30 Fixed jackset, reversed	30 Fixed jackset, reversed
19 Two fixed jackscrews	19 Two fixed jackscrews
20 Two fixed jacksockets	20 Two fixed jacksockets
59 Hex turning jackset, .200"	59 Hex turning jackset, .200"
60 Hex turning jackset, reversed, .200"	60 Hex turning jackset, reversed, .200"
61 Two hex turning jackscrews, .200"	61 Two hex turning jackscrews, .200"
62 Two hex turning jacksockets, .200"	62 Two hex turning jacksockets, .200"
64 Turning jackset, .490"	64 Turning jackset, .490"
65 Turning jackset, reversed, .490"	65 Turning jackset, reversed, .490"
66 Two turning jackscrews, .490"	66 Two turning jackscrews, .490"
67 Two turning jacksockets, .490"	67 Two turning jacksockets, .490"

POLARIZATION:	POLARIZATION
00 None	00 None
01 thru 68 are special identifiers, see R-38	01 thru 68 are special identifiers, see R-38
70 Same configuration as 01 without Loctite® (To be keyed by customer)	70 Same configuration as 01 without Loctite® (To be keyed by customer)

OPTIONS

BN Bond #1-72, sm. pattern hex nuts into mtg. ears

☒ = Option not RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AirBorn:

[RM322-080-201-5900](#) [RM322-071-212-2000](#) [RM322-092-231-5503](#) [RM322-122-203-2900](#) [RM342-047-221-8000](#)
[RM352-104-321-5502BN](#) [RM322-104-211-5503](#) [RM342-035-581-6100](#) [RM342-140-241-5500](#) [RM372-182-321-5500](#)
[RM322-023-212-5700](#) [RM322-059-571-5700](#) [RM322-140-211-5501](#) [RM342-023-241-5500](#) [RM342-011-591-2000](#)
[RM342-035-571-5800](#) [RM342-047-221-0256](#) [RM352-092-312-5500](#) [RM322-122-221-5503](#) [RM352-071-321-2900BN](#)
[RM322-035-651-3000](#) [RM322-035-651-5500](#) [RM322-104-211-5502](#) [RM322-206-222-5501](#) [RM342-023-201-8400](#)
[RM342-182-221-5500](#) [RM352-104-311-5501BN](#) [RM352-152-322-8000](#) [RM352-182-321-5500BN](#) [RM342-047-203-](#)
[5500](#) [RM352-182-331-5501BN](#) [RM352-182-331-5564BN](#) [RM372-035-323-5900](#) [RM322-122-241-5565](#) [RM352-122-](#)
[371-5570](#) [RM352-059-331-2000](#) [RM322-092-541-5500](#) [RM352-011-321-5501](#) [RM352-092-311-2900BN](#) [RM372-047-](#)
[312-8000](#) [RM372-071-321-5500](#) [RM322-011-241-1900](#) [RM342-059-651-2900](#) [RM352-122-331-5503](#) [RM342-023-](#)
[213-2900](#) [RM342-035-201-2900](#) [RM342-059-551-0256](#) [RM352-104-311-5503BN](#) [RM372-047-312-5900](#) [RM322-104-](#)
[212-5570](#) [RM322-182-221-5564](#) [RM342-035-241-6000](#) [RM342-047-581-6000](#) [RM352-023-322-5500](#) [RM352-071-](#)
[321-6100](#) [RM372-023-322-5800](#) [RM322-035-231-2900](#) [RM322-047-241-8400](#) [RM342-080-571-2900](#) [RM322-023-](#)
[231-5500](#) [RM342-023-202-8400](#) [RM342-080-201-2900](#) [RM352-152-311-5565](#) [RM352-182-331-5532BN](#) [RM342-059-](#)
[571-2900](#) [RM322-023-581-2900](#) [RM322-035-571-5800](#) [RM322-182-201-5517](#) [RM322-182-221-5532](#) [RM342-080-](#)
[241-6000](#) [RM352-011-332-2900](#) [RM352-140-311-5501](#) [RM352-140-321-5700](#) [RM352-152-321-5502BN](#) [RM322-059-](#)
[221-5900](#) [RM322-059-641-3000](#) [RM322-140-211-5502](#) [RM342-023-221-2900](#) [RM342-023-571-6000](#) [RM342-059-](#)
[581-5500](#) [RM352-035-311-3000](#) [RM352-047-371-5500](#) [RM322-071-571-5800](#) [RM342-023-581-6100](#) [RM342-035-](#)
[213-5900](#) [RM342-059-202-2900](#) [RM352-080-311-3000](#) [RM352-104-311-5503](#) [RM352-059-322-2900BN](#) [RM352-122-](#)
[331-5502](#) [RM322-059-201-8400](#) [RM322-122-221-5511](#) [RM342-023-581-6000](#) [RM342-059-581-7200](#) [RM342-071-](#)
[571-5800](#) [RM352-047-321-5501](#) [RM352-122-331-5511](#) [RM322-035-641-2900](#) [RM322-047-212-1900](#) [RM322-104-](#)
[201-0256](#)