

Cable to Board (Standard Footprint)

.050"

9 thru 100 Contacts

Rugged Cable


MM, MN

Rugged Board Mount

MK, ML


MM-322-051-261-45WP
(METAL)

MN-321-051-261-45WP
(PLASTIC)



MK-332-051-125-2200
(METAL)

ML-331-051-125-2200
(PLASTIC)



PLUG

RECEPTACLE

DIMENSIONS													
SIZE	CONTACT ROWS	A	B		C	D	E	H	P	X	Y	Z**	HARDWARE
			PLUG MAX	RCPT MAX			POTTING WELL MAX						
9	2	.775	.334	.400	.390	.565	.270	.298	.210	.298	.280	.390	#2-56 UNC THD (#2-56 CLEARANCE OR #2-56 UNC THREADED INSERT)
15		.925	.484	.550	.540	.715						.540	
21		1.075	.634	.700	.690	.865						.690	
25		1.175	.734	.800	.790	.965						.780	
31		1.325	.884	.950	.940	1.115			.930				
37	3	1.475	1.034	1.100	1.090	1.265	.310	.341	.214	.390	.330	1.080	#4-40 UNC THD (#4-40 CLEARANCE OR #4-40 UNC THREADED INSERT)
51		1.425	.984	1.050	1.040	1.215			1.046				
69		1.725	1.284	1.350	1.340	1.515			1.346				
100	4	2.160	1.384	1.508	1.432	1.800	.360	.384	.216	.490	.379	1.530	

* = 69 POSITION CONNECTORS ARE AVAILABLE IN METAL ONLY.

** = "Z" DIMENSION FOR TURNING JACKSCREW ONLY

* = 69 POSITION CONNECTORS ARE AVAILABLE IN METAL ONLY.
** = "Z" DIMENSION FOR TURNING JACKSCREW ONLY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[MK-232-025-133-0000-0B7](#)