



Rugged Metal Solder Cup (Integral Shield Termination)

.050"

9 thru 100 Contacts

MM


MATING MATRIX	
CONNECTOR	MATES WITH
MM-2P...	MK, ML, MM, MN receptacles
MM-2Q...	MK, ML, MM, MN plugs



FLAT WASHER, HELICAL LOCK WASHER,
SPANNER NUT, (2 PLCS)
#2-56 JACKPOST ASSY, (2 PLCS)

MM-2P2-031-113-4500
(PLUG)

MM-2Q2-031-213-2200
(RECEPTACLE)



DIMENSIONS																	
SIZE	CONTACT ROWS	A		B		C	HARDWARE	D	E	F	G	H	I	J		K	
		PLUG MAX	RCPT MAX	PLUG MAX	RCPT MAX									PLUG	RCPT	PLUG	RCPT
9	2	.185	.251	.334	.400	.565	#2-56 UNC THD (.092 DIA THRU)	.775	.298	.340	.335	.375	.440	.183	.195	.640	.652
15				.484	.550	.715		.925				.525	.590				
21				.634	.700	.865		1.075				.675	.740				
25				.734	.800	.965		1.175				.775	.840				
31				.884	.950	1.115		1.325				.925	.990				
37				1.034	1.100	1.265		1.475				1.075	1.140				
51	3	.228	.294	1.384	1.450	1.615		1.825	.341	.380	.367	1.425	1.490	.183	.195	.640	.652
51				.984	1.050	1.215		1.425				1.025	1.090				
69				1.284	1.350	1.515		1.725				1.325	1.390				
100	4	.271	.394	1.384	1.508	1.800	#4-40 UNC THD (.147 DIA THRU)	2.160	.381	.430	.417	1.457	1.522				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[MM-4P3-100-113-8100](#)