

PLUG: WTA 20 PC JT
 RECEPTACLE: WTA 20 SAD9 JL
 XXX XX XXXX XX

PLUG		RECEPTACLE		XXX	XX	XX
SERIES						
WTA	Plug, straight, no mounting ears		WTA	Receptacle, straight, no mounting ears		
SIZE						
XX	Number of contacts (10, 14, 20, 24, 26, 30, 36, 40, 44, 50, 54, 56, 60, 66, or 70)		XX	Number of contacts (10, 14, 20, 24, 26, 30, 36, 40, 44, 50, 54, 56, 60, 66, or 70)		
CONTACTS						
<ul style="list-style-type: none">Pin or socket contacts can be used in either plug or receptacle.When pin contacts are used, standard hardware orientation places the female hardware next to the #1 pin contact.When socket contacts are used, standard hardware orientation places the male hardware next to the #1 socket contact.						
TYPE CONTACTS/TERMINATIONS:			TYPE CONTACTS/TERMINATIONS:			
PC	Pin, straight, solder cup (.035" I.D.)		SAC	Socket, straight, solder cup (.035" I.D.)		
PD5	Pin, straight, dip solder, .078" x .027" dia		SAD7	Socket, straight, dip solder, .109" x .027" dia		
PD7	Pin, straight, dip solder, .109" x .027" dia		SAD9	Socket, straight, dip solder, .140" x .027" dia		
PD9	Pin, straight, dip solder, .140" x .027" dia		SAD11	Socket, straight, dip solder, .172" x .027" dia		
PD11	Pin, straight, dip solder, .172" x .027" dia		SAF3	Socket, straight, flex circuit, .050"		
PD13	Pin, straight, dip solder, .203" x .027" dia		SAF6	Socket, straight, flex circuit, .093"		
PD15	Pin, straight, dip solder, .234" x .027" dia		SAF9	Socket, straight, flex circuit, .140"		
PD20	Pin, straight, dip solder, .312" x .027" dia		SAG7	Socket, straight, dip solder, .109" x .018" dia		
PF3	Pin, straight, flex circuit, .050"		SAG9	Socket, straight, dip solder, .140" x .018" dia		
PF6	Pin, straight, flex circuit, .093"		SAG11	Socket, straight, dip solder, .172" x .018" dia		
PF8	Pin, straight, flex circuit, .125"		SAP	Socket, straight, pin termination, .150" (connector saver)		
PW34	Pin, straight, wire wrap® ,.531"		SAW24	Socket, straight, wire wrap® ,.375"		
PW40	Pin, straight, wire wrap® ,.625"		SAW40	Socket, straight, wire wrap® ,.625"		

HARDWARE	
<ul style="list-style-type: none"> Jackset hardware determines image of connector. Must specify image with guide set hardware. Plug facial seal gaskets and hoods; order separately or add "Q" in part number. Example: WTA10PD9QJ. See "Gaskets" and "Hoods" in Accessories section for instructions. Fixed jackset, long (JL) includes jackscrew or jacksocket, #2-56 nut, #2 flat washer & #2 lockwasher. 	
JT	Turning jackset, .500"
JTA	Turning jackset, .200"
JTB	Hex turning jackset, .200"
JTC	Hex turning jackset, .500"
JTL	Turning jackset, .700"
J	Fixed jackset
JL	Fixed jackset, long

OPTIONS	
<ul style="list-style-type: none"> Option Codes: Add to the end of the part number. Example: WTA10SAD9J-D01. Call factory for additional codes. 	
-443	Polarizing pin installed in contact position noted by dash number. See "Polarization" in Accessories section.
-444	Contact position noted by dash number is left open (to mate with -443). See "Polarization" in Accessories section.
-B82	Termination face sealed against conformal coating
-D01	Pretinned contact terminations (except solder cups, wire wraps [®] and flex contacts) with 63/37 or 60/40 solder. <input checked="" type="checkbox"/>
-P39	Pretinned contact terminations (except solder cups, wire wraps [®] and flex contacts) with SAC305 solder (lead free).
-D54	Combine -B82 & -D01 options
-G69	Solder cups fixed in an outward orientation (otherwise contacts will rotate)
<input checked="" type="checkbox"/> = Option not RoHS compliant	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AirBorn:

[WTA56PCJTB](#) [WTA60SACJ](#) [WTA36PCJTB](#) [WTA70SACJ](#) [WTA66SAD9J](#) [WTA66PCJTB](#) [WTA70PCJTB](#)
[WTA70PD9JTB](#) [WTA30SAD9J](#) [WTA36SAD9J](#) [WTA54PCJTB](#) [WTA30SACJ](#) [WTA44PCJTB](#) [WTA40SACJ](#)
[WTA44SAD9J](#) [WTA50PCJTB](#) [WTA40SAD9J](#) [WTA50SACJ](#) [WTA36SACJ](#) [WTA50SAD9J](#) [WTA60PCJTB](#)
[WTA40PCJTB](#) [WTA60SAD9J](#) [WTA40PD9JTB](#) [WTA10PD9JTB](#) [WTA14PD9JTB](#) [WTA20PD9JTB](#) [WTA30PD9JTB](#)
[WTA36PD9JTB](#) [WTA44PD9JTB](#) [WTA56SACJ](#) [WTA56SAD9J](#) [WTA60PD9JTB](#) [WTA66PD9JTB](#) [WTA66SACJ](#)
[WTA70SAD9J](#) [WTA44SACJ](#) [WTA50PD9JTB](#) [WTA54PD9JTB](#) [WTA54SACJ](#) [WTA54SAD9J](#) [WTA56PD9JTB](#)