



PLUG: WBB50PMT
RECEPTACLE: WB50SD6
XXXXXXXXXXXX

PLUG

RECEPTACLE

SERIES

WBB 2 row, SMT, plug, with mounting ears	WB 2 row, straight, receptacle, with mounting ears
WBA 2 row, SMT, plug, full skirt, with mounting ears	

SIZE

20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132	20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132
--	--

CONTACTS

TYPE CONTACTS/TERMINATIONS:		TYPE CONTACTS/TERMINATIONS:	
PMT	Pin, card edge SMT (Board: .054/.070)	SD6	Socket, straight, dip solder, .095"
		SD9	Socket, straight, dip solder, .140"
		SD12	Socket, straight, dip solder, .190"
		SD19	Socket, straight, dip solder, .300"

HARDWARE

STYLE OF HARDWARE: (See WB-9)		STYLE OF HARDWARE: (See WB-9)	
K*_*	Integral keying guides, polarized	K*_*	Integral keying guides, polarized
KY*_*	Stainless steel keying guides, polarized	KY*_*	Stainless steel keying guides, polarized
JMM	2 stainless steel fixed jackscrews	JTFF	2 stainless steel turning jackscrews

DIMENSIONS					
SIZE	A	B	C	D	E
20	1.150	.900	.450	1.030	.750
30	1.400	1.150	.700	1.280	1.000
40	1.650	1.400	.950	1.530	1.250
50	1.900	1.650	1.200	1.780	1.500
60	2.150	1.900	1.450	2.030	1.750
70	2.400	2.150	1.700	2.280	2.000
80	2.650	2.400	1.950	2.530	2.250
90	2.900	2.650	2.200	2.780	2.500
100	3.150	2.900	2.450	3.030	2.750
110	3.400	3.150	2.700	3.280	3.000
128	3.850	3.600	3.150	3.730	3.450
132	3.950	3.700	3.250	3.830	3.550

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AirBorn:

[M55302/119-11](#) [M55302/119-10](#) [M55302/119-06](#) [M55302/119-07](#) [WTB24PR7J342](#) [M55302/119-09](#) [M55302/58-A20F](#) [M55302/61A24](#) [M55302/57-B56X](#) [M55302/57-A44Y2](#) [M55302/57-A44Y1](#) [M55302/57-A44Y5](#) [M55302/57-A66H](#)
[M55302/57-A50Y1](#) [M55302/57-B44H](#)