



AX60552

8-Slot ShoeBox Chassis

Features

- Two 5.25" and one 3.5" HDD drive bays
- Desktop or wallmount industrial computer chassis
- Equipped with PS/2 type power supply



Specifications

Standard Color	Beige color
Construction	Heavy-duty steel
Drive Capacity	Exposed 2 x 5.25" HDD drive bay and 1 x 3.5" HDD drive bay
Cooling	1 x 12 cm ball-bearing fan (88 CFM/each) with a removable filter
Front Panel Indicators	1 x power on/off; 1 x HDD
Front Panel Controls	1 x power on/off, 1 x system reset
Front Panel Connectors	2 x USB
Pre-punched Panel Rear	1 x 9-pin ; 1 x 25-pin
System Board	Full-size SBCs

Expansion Interface	8-slot backplane
Power Supply	PS/2 power supply
Speaker	1 x 0.4W speaker
Operating Temperature	0°C ~ +40°C (+32°F ~ +104°F)
Dimensions	368.8 mm (14.52") (W) x 407.5 mm (16.04") (D) x 177.3 mm (6.98") (H)
Weight (net/gross)	10.5 kg (23.15 lb)/11.3 kg (24.92 lb)

Power Supply Specifications

Items	Watt	Input	Specifications Output	MTBF
PS302-XP2	ATX 300W (PFC)	AC 100~240V (Auto)	+5V @ 16A +12V1 @ 17A +12V2 @ 17A +5VSB @ 2.5A +3.3V @ 19A -12V @ 0.3A	100,000 hours
PS400-XP2	ATX 400W (PFC)	AC 90~264V (Auto)	+5V @ 20A +3.3V @ 20A +12V1 @ 16A +12V2 @ 16A -12V @ 0.5A +5VSB @ 2.5A	100,000 hours
PS500-XP2	ATX 500W (PFC)	AC 90~264V (Auto)	+5V @ 24A +3.3V @ 24A +12V @ 34A +12V1 @ 17A +12V2 @ 17A -12V @ 0.8A +5VSB @ 2.5A	100,000 hours

Ordering Information

AX60552WB/X300	With ATX 300W power supply
AX60552WB/X400	With ATX 400W power supply
AX60552WB/X500	With ATX 500W power supply

*Specifications and certifications are based on options and may vary.

Backplane Options


PICMG 1.0

Models	Slots per Segment (ISA/PCI/PCIe/CPU)	Segment
ATX6022/8GP7	0/7/0/1	Single
ATX6022/8	3/4/0/1	Single

PICMG 1.3

Models	Slots per Segment (ISA/PCI/PCIe/CPU)	Segment
FAB111	0/4/2/1	Single
FAB208	0/6/1/1	Single
HAB208	0/6/1/1	Single
FAB116	0/3/4/1	Single

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[AX60552WB-NP B/P Ver w/o Power,chassis](#)