


eBOX621-831-FL

Fanless Embedded System with Intel® Atom™ Processor N270 1.6 GHz and 9 ~ 34VDC Input



▲ Front view



Specifications

Standard Color	Silver-Black
Construction	Aluminum extrusion and heavy-duty steel, IP40
CPU	Intel® Atom™ processor N270 1.6 GHz
System Memory	1 x 200-pin DDR2 SO-DIMM max. up to 2 GB
Chipset	Intel® 945GSE + ICH7M
BIOS	AMI 8Mbit with RPL/PXE LAN boot ROM
System I/O Outlet	3 x RS-232 (COM 1/2/3) 1 x VGA 1 x Audio (Mic-in/Line-out) 1 x PS/2 keyboard/mouse 2 x 10/100/1000Mbps Ethernet (Realtek RTL8111B) 4 x USB 2.0 1 x VDC power input connector 1 x ATX power switch
Watchdog Timer	255 levels, 1 ~ 255 sec.
Storage	1 x 2.5" SATA HDD drive bay 1 x CompactFlash™ slot
Expansion Interface	N/A
System Indicator	1 x green LED for system power-on 1 x orange LED for HDD active
Power Supply	42.5W 9 ~ 34VDC
Operating Temperature	-10°C ~ +50°C (14°F ~ 122°F) (with 1.6 GHz CPU, W.T. HDD)
Storage Temperature	-20°C ~ +80°C (-4°F ~ +176°F)
Humidity	10% ~ 90%, non-condensing
Vibration Endurance	2 Grms with CF (5 - 500 Hz, X, Y, Z directions)
Dimensions	200 mm (7.87") (W) x 120 mm (4.72") (D) x 56 mm (2.2") (H)
Weight (net/gross)	1.8 kg (3.97 lb)/2.6 kg (5.73 lb)
Certification	CE
EOS Support	XPE, WinCE, Linux, WES, WES7

* XPE: Windows® XP Embedded

* WES: Windows® XP Embedded Standard

* WES7: Windows® Embedded Standard 7

* WES8: Windows® Embedded Standard 8

Packing List

- 1 x quick manual
- 1 x driver CD
- 1 x Y cable for PS/2 keyboard/mouse
- 1 x screw pack
- 4 x foot pad
- 2 x CF mylar
- 1 x DC-in connector

Features

- Intel® Atom™ processor N270 1.6 GHz onboard
- Intel® 945GSE + ICH7M chipset
- Fanless operation design with full feature I/O
- One 2.5" SATA drive bay
- 9 ~ 34VDC wide range DC input



▲ Rear view

Power Protection

DC Version

- EMI suppression filter
- OVP (over voltage protection)
- UVP (under voltage protection)
- OCP (over current protection)
- Reverse protection

Ordering Information

Standard


eBOX621-831-FL-1.6G	Fanless embedded system with Intel® Atom™ processor N270 1.6 GHz, 9 ~ 34VDC input
eBOX621-831-FL-1.6G w/o Logo	Fanless embedded system with Intel® Atom™ processor N270 1.6 GHz, 9 ~ 34VDC input and w/o logo

Optional

2.5" SATA HDD	40 GB or above
2.5" SATA SSD	4 GB or above
DDR2 SODIMM	256 MB ~ 2 GB
CompactFlash™	256 MB or above
Din rail kit	
Wall mount kit	
VESA mount kit	

*Specifications and certifications are based on options and may vary.

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[eBOX621-831-FL1.6G-RC-DC](#)