


MVS900-511-FL

Fanless Vision System with LGA1151 Socket 7th/6th Gen Intel® Core™ i7/i5/i3 & Celeron® Processor, Intel® H110, Vision I/O, 4-CH PoE and 4-CH LED Output

Features

- Integrated real-time vision I/O
 - 4-CH trigger input
 - 4-CH trigger output
 - 4-CH LED lighting control
 - 2-CH quadrature encoder input
 - 16-CH isolated DIO
- Supports camera interfaces
 - 4 IEEE802.3at GbE LAN ports (PoE)
- Power input: 24 VDC (uMin=19V/uMax=30V)
- -10°C to +60°C operating temperature range with W.T. SSD
- Supports 2 swappable 2.5" HDD
- Supports TPM 2.0 function



- | | | |
|----------------------|----------------------------------|---|
| 1. Reset switch | 7. 2 x RS-232/422/485 | 11. Vision I/O: 4-in/4-out trigger I/O, |
| 2. Remote switch | 1 x 8-in/8-out DIO with isolated | 8-in/8-out DIO, 2 x encoder |
| 3. Mic-in & Line-out | 1.5 kVDC protection | 12. LED lighting control: trigger and |
| 4. 2 x LAN | 8. VGA | strobe mode |
| 5. Power switch | 9. 4 x USB 3.0 | 13. 4 x IEEE802.3at GbE LAN port |
| 6. Terminal block | 10. HDMI | |



Specifications

Standard Color	Black
Construction	Aluminum die-casting and heavy-duty, IP40
Processor System	CPU Level 7th/6th gen Intel® Core™ i7/i5/i3 & Celeron® processors, up to 65W (Kaby Lake/SkyLake)
	Chipset Intel® H110
System Memory	2 x DDR4-2133/2400 un-buffered SO-DIMM, up to 32GB
System I/O	1 x Switch for power On/Off (ATX)
	1 x Remote switch
	1 x Reset switch
	1 x 3-pin terminal block
	1 x ATX/ATX selectable switch
	2 x 10/100/1000 Mbps Ethernet (Intel® i211-AT)
	2 x RS-232/422/485 & 1 x 8-in/8-out DIO with isolated 1.5 kVDC protection
	4 x USB 3.0
	1 x HDMI
	1 x VGA
	1 x Mic-in
	1 x Line-out
TPM	TPM 2.0
Vision I/O	- 4-CH trigger input (response time<1us, sink type, input range: 0 to 30V)
	- 4-CH trigger output (response time<1us, sink type, open collector, output range: 0 to 30V, 100mA max./CH)
	- 4-CH LED lighting control (strobe mode: 24V, 1A per CH/ trigger mode: 24V, 0.5A per CH)
	- 2-CH quadrature encoder input (A/B/Z)
	- 8-CH isolated DI (sink/source type, input range: 0 to 30V)
	- 8-CH isolated DO(sink type, open collector, supply voltage: 5-30V, 200mA max./CH)
	- Programmable interrupt functions

Camera Interface	4 x IEEE802.3at GbE LAN port (PoE, Intel® i210-AT, IEEE802.3at compliant, total max. power output 30W)
Expansion Interface	1 x Full-size PCI Express Mini Card slot with USB signal 1 x Internal USB connector
Storage	2 x 2.5" swappable HDD (9.5 mm height)
System Indicators	1 x Power LED 1 x HDD LED 4 x PoE power LED
Power Input	Type: ATX/AT Input: 24 VDC (uMin=19V/uMax=30V)
Operating Temperature	-10°C to +60°C (+14°F to +140°F) with 6th gen Intel® Core™ up to 35W and W.T. HDD/SSD* -10°C to +50°C (+14°F to +112°F) with 6th/7th gen Intel® Core™ up to 65W and W.T. HDD/SSD*
Storage Temperature	-20°C to +80°C (-4°F to +176°F)
Humidity	10% to 90%, non-condensing
Dimensions	135 mm (5.31") (W) x 208 mm (8.19") (H) x 230 mm (9.06") (D)
Weight (net/gross)	5 kg (11.02lb)/5.9 kg (13 lb)
Certifications	CE, FCC
Software Support	AMS.AXView

* CPU support list please refer to the user's manual

Ordering Information

System

MVS900-511-FL (P/N: E27L900100)	Fanless vision system with LGA1151 socket 7th/6th gen Intel® Core™ i7/i5/i3 & Celeron® processor, Intel® H110, vision I/O, 4-CH PoE and 4-CH LED output
------------------------------------	---

Optional Accessory

2.5" SATA HDD/SSD	
DDR4-2133/2400 un-buffered SO-DIMM, up to 32GB	
8817L900010E	MVS900-511 usb dongle kit
8817L900020E	MVS900_BK_Din_Kit
8817L900030E	MVS900_Wall-Mount_Kit
5A244AP1200E	44-pin DIN-rail terminal board DM44-AP12
594DM443500E	44-pin D-SUB cable, L=1m WHDM44/1.0-6954
594DM443510E	44-pin D-SUB cable, L=2m WHDM44/2.0-6954
594DM443520E	44-pin D-SUB cable, L=3m WHDM44/3.0-6954

* Specifications and certifications may vary based on different requirements.

Power Protection


DC Version

OVP (over voltage protection)
SCP (short circuit protection)
OCP (over current protection)

Packing List

- 1 x MVS900-511-FL
- 1 x Screw pack
- 4 x Foot pad
- 1 x CPU grease
- 1 x Terminal block
- 1 x Remote power switch cable

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[MVS900-511-FL](#) [MVS900_BK_Din_Kit](#) [MVS900_Wall-Mount_Kit](#) [MVS900-511 usb dongle kit](#)